


Engineer Drawing

Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 5A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: $\geq 1000M\Omega$
- Contact resistance: $\leq 10m\Omega$
- After environmental testing: $\leq 20m\Omega$
- Plating category: G-Contact Gold Flash
S-Bright plating
- Material: PT-PBT 94V-0



Poles	Dimensions (mm)	
	A	B
2*01	--	6.65
2*02	3.00	9.65
2*03	6.00	12.65
2*04	9.00	15.65
2*05	12.00	18.65
2*06	15.00	21.65
2*07	18.00	24.65
2*08	21.00	27.65
2*09	24.00	30.65
2*10	27.00	33.65
2*11	30.00	36.65
2*12	33.00	39.65

Scale 1:3

IPCW300W** * * * *
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series Type
- ② Pin code.
- ③ Material code.
- ④ Appearance code.
- ⑤ Internal code
- ⑥ Company code.
- ⑦ Other code.

TOLERANCE

.X ± 0.30
.XX ± 0.20
.XXX ± 0.10

UNLESS OTHERWISE SPECIFIED

NCP

PART NO.
IPCW300W-R
DRAWING NO.
IPCW300W-R

www.i-ncp.com

TITLE:
Pitch 3.0mm wafer angle








SHEET 1 OF 1


UNITS mm

SCALE 1:1


REV. 01



2P P.C.B LAYOUT



4P~6P P.C.B LAYOUT



8P~24P P.C.B LAYOUT