

## SGM449 2.7V to 10V, SOT-23 Temperature Sensor

### **GENERAL DESCRIPTION**

The SGM449 can detect the temperature from -55°C to +150°C and its operation voltage level is from 2.7V to 10V. For the output voltage stage, the DC offset voltage is equal to 600mV at 0°C and it changes linearly with 10mV/°C. The beneficial of the positive offset voltage is that it can allow the SGM449 to read negative temperature accurately. For measuring the temperature range from -55 °C to +150 °C, the corresponding nominal output voltage range is from 50mV to 2.1V. The SGM449 is calibrated to achieve the accuracy of  $\pm 1$  °C (MAX) at +25 °C and  $\pm 2$  °C (MAX) at full measureable range of temperature.

The SGM449 can simplify the required external circuit for the measurement of negative temperature through its excellent linearity, positive offset voltage and calibration of factory. A class-AB output driver provides a strong 500 $\mu$ A maximum output to drive capacitive loads up to 2000pF and is designed to directly interface to analog-to-digital converter sample and hold inputs. The quiescent current of the device is 26 $\mu$ A (TYP), which means that its temperature caused by the 26 $\mu$ A quiescent current is within 0.1 °C in still air. The shutdown capability which is inside the SGM449 allows it to be powered by MCU directly as its low consumption of power.

The SGM449 is available in a Green SOT-23 package and specified over the extended -55 °C to +150 °C temperature range.

## **FEATURES**

- 2.7V to 10V Supply Voltage Range
- Temperature Accuracy:
- +25°C: ±1°C (MAX)
- -55°C to +150°C: ±2°C (MAX)
- Offset Output Voltage: 600mV at 0°C (TYP)
- Calibrated Linear Scale Factor: 10mV/°C
- Current Drain at +25°C: 26µA (TYP)
- Nonlinearity: ±0.5°C (MAX)
- Strong Output for Driving Loads up to 2000pF
- Short-Circuit Protection Output
- Suitable for Remote Applications
- Available in a Green SOT-23 Package

### **APPLICATIONS**

Mobile Phones and Laptops Modules of Power Supply Battery Management Fax Machines and Printers HVAC and Disk Drives

## SIMPLIFIED SCHEMATIC



**Figure 1. Simplified Schematic** 



## **PACKAGE/ORDERING INFORMATION**

MODEL	PACKAGE DESCRIPTION	SPECIFIED TEMPERATURE RANGE ORDERING NUMBER		PACKAGE MARKING	PACKING OPTION
SGM449	SOT-23	-55°C to +150°C	SGM449TN3LG/TR	ORCXX	Tape and Reel, 3000

#### MARKING INFORMATION

NOTE: XX = Date Code.							
<u>YYY X</u>	X						
	Date Code - Week						
	—— Date Code - Year						
	—— Serial Number						

Green (RoHS & HSF): SG Micro Corp defines "Green" to mean Pb-Free (RoHS compatible) and free of halogen substances. If you have additional comments or questions, please contact your SGMICRO representative directly.

### **ABSOLUTE MAXIMUM RATINGS**

Supply Voltage Range	0.2V to 12V
Output Voltage Range	0.3V to 6V
Output Current Range	2mA to 2mA
Latch-up Current Range, Each Pin	150mA to 150mA
Package Thermal Resistance	
SOT-23, θ <sub>JA</sub>	290°C/W
Junction Temperature	+150°C
Storage Temperature Range	65°C to +150°C
Lead Temperature (Soldering, 10s)	+260°C
ESD Susceptibility	
НВМ	4000V
CDM	1000V

#### **RECOMMENDED OPERATING CONDITIONS**

Supply Voltage Range, $V_{DD}$	2.7V to 10V
<b>Operating Ambient Tempera</b>	ture55°C to +150°C

#### **OVERSTRESS CAUTION**

Stresses beyond those listed in Absolute Maximum Ratings may cause permanent damage to the device. Exposure to absolute maximum rating conditions for extended periods may affect reliability. Functional operation of the device at any conditions beyond those indicated in the Recommended Operating Conditions section is not implied.

#### ESD SENSITIVITY CAUTION

This integrated circuit can be damaged if ESD protections are not considered carefully. SGMICRO recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage. ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because even small parametric changes could cause the device not to meet the published specifications.

#### DISCLAIMER

SG Micro Corp reserves the right to make any change in circuit design, or specifications without prior notice.



## **PIN CONFIGURATION**



## **PIN DESCRIPTION**

PIN	NAME	FUNCTION
1	VDD	Positive Power Supply Pin.
2	VO	Output Voltage Pin. The output voltage is proportional to measured temperature.
3	GND	Ground.



## **ELECTRICAL CHARACTERISTICS**

( $V_{DD}$  = 2.7V to 10V,  $T_A$  = -55°C to +150°C, GND = Ground and no load, unless otherwise noted.)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS	
Power Supply							
Operating Current		$T_{A} = +25^{\circ}C, V_{DD} = 3V$		26	39		
Operating Current	I <sub>DD</sub>	T <sub>A</sub> = +150°C		36	49	μA	
Line Regulation	$\Delta^{\circ}C/\Delta V_{DD}$		-0.08	±0.02	0.08	°C/V	
Sensor Accuracy							
Temperature Accuracy (1)	т	T <sub>A</sub> = +25°C	-1	±0.5	1	°C	
Temperature Accuracy	T <sub>ACC</sub>	T <sub>A</sub> = -55°C to +150°C	-2	±0.5	2		
Sensor Output				-			
Offset Output Voltage	V <sub>OFFS</sub>	$T_A = 0^{\circ}C$		600		mV	
Temperature Coefficient (Sensor Gain)	Tc			10		mV/°C	
Output Nonlinearity <sup>(1)</sup>	V <sub>ONL</sub>	T <sub>A</sub> = -55°C to +150°C, no load		±0.5		°C	
Output Current	I <sub>OUT</sub>				500	μA	
Output Impedance	7	I <sub>OUT</sub> = 100μA, f = 100Hz	4				
Output impedance	Z <sub>OUT</sub>	I <sub>OUT</sub> = 100μA, f = 500Hz		9		Ω	
Output Load Regulation		$T_A$ = -55°C to +150°C, $I_{OUT}$ = 100µA, $\Delta V_{OUT}/\Delta I_{OUT}$		0.2		Ω	
Power-On Time	t <sub>on</sub>	Time to reach accuracy within ±0.5℃		310	620	μs	
Typical Load Capacitance	C <sub>LOAD</sub>				2000	pF	

#### NOTE:

1. The accuracy of the temperature is essential and it is the voltage difference between the measured and the output voltage. The line regulation also should be taken into consideration as the accuracy limits. However, the effect of DC load (load regulation) is not considered as the accuracy limit is for no load case.



## **TYPICAL PERFORMANCE CHARACTERISTICS**

 $T_A$  = +25°C, unless otherwise noted.



## **TYPICAL PERFORMANCE CHARACTERISTICS (continued)**

 $T_A$  = +25°C, unless otherwise noted.









### FUNCTIONAL BLOCK DIAGRAM



Figure 2. Block Diagram

## **DETAILED DESCRIPTION**

#### Overview

The SGM449 can detect the temperature from -55°C to +150°C and its operation voltage level is from 2.7V to 10V. For the output voltage stage, the DC offset voltage is equal to 600mV at 0°C and it changes linearly with 10mV/°C. The beneficial of the positive offset voltage is that it can allow the SGM449 to read negative temperature accurately. For measuring the temperature range from -55 °C to +150 °C, the corresponding nominal output voltage range is from 50mV to 2.1V. The SGM449 is calibrated to achieve the accuracy of  $\pm 1$  °C (MAX) at +25 °C and  $\pm 2$  °C (MAX) at full measureable range of temperature. The delta-VBE architecture is comprised inside the device. And there is a buffer between the output stage and the temperature sensing parts.

#### **Feature Description**

#### SGM449 Transfer Function

The following equation is a linear transfer function that is used for calculating the  $V_{\text{OUT}}$  of SGM449, the output voltage is proportional to the measured temperature.

$$V_{out} = 10(mV/^{\circ}C) \times T(^{\circ}C) + 600(mV)$$
 (1)

Where T is the temperature in  $^\circ C$  and  $V_{OUT}$  is the output voltage of VO pin.

Table 1. Temperature and Typical VOUT Values

Temperature	V <sub>OUT</sub> (TYP)
+150°C	2100mV
+125°C	1850mV
+100°C	1600mV
+85°C	1450mV
+25°C	850mV
0°C	600mV
-25°C	350mV
-30°C	300mV
-50°C	100mV
-55°C	50mV

#### **Device Functional Mode**

Analog output proportional to temperature is the only functional mode of the SGM449.



## **APPLICATION INFORMATION**

Because of the advantages of low power consumption and high supply voltage range, the SGM449 can be used in the applications that measuring extreme positive and negative temperatures with single power supply.

### **Typical Temperature Sensing Circuit**



Figure 3. Typical Temperature Sensing Circuit

#### **Design Requirements**

Table 2 lists the recommended input parameters of Figure 3.

#### Table 2. Design Parameters

Parameter	Value		
Power Supply Voltage	2.7V to 10V		
Accuracy at +25°C	±1°C (MAX)		
Accuracy over -55°C to +150°C	±2°C (MAX)		
Temperature Slope	10mV/°C		

#### **Capacitive Loads**

For noisy conditions, such as driving a SAR ADC, an output capacitor is necessary to filter out output noise due to the switching input of the load. Also, the ability of the capacitive loading is excellent for the SGM449. In Figure 4, the SGM449 can handle a 2000pF capacitive load. However, if the load capacitance is larger than 2000pF, a series resistor should be used to compensate for the SGM449. If the C<sub>L</sub> value is 2nF to 1 $\mu$ F, the minimum value of R<sub>S</sub> should be 800 $\Omega$ .



Figure 4. Application Circuit for Capacitive Loading Less than 2000pF



Figure 5. SGM449 with Series Resistor for Capacitive Loading Greater than 2000pF

#### **Power Supply Recommendations**

To reduce the effect of a noisy power supply, an RC filter can be used to decrease the noise pick-up. And a  $0.1\mu$ F capacitor should be taken into account.

### Other Application Circuits

Centigrade Thermostat Application

The hysteresis comparator can be used to indicate high or low state for different temperatures. Before designing the example in this section, it is recommended that the customers need to test and validate the circuit. The parameters in the section of Typical Temperature Sensing Circuit can be taken into account unless any noted specifications.







## **APPLICATION INFORMATION (continued)**

#### **Conserving Power Dissipation with Shutdown**

The SGM449 can be shutdown with an output of a logic gate because of its ultra-low power dissipation.



Figure 7. Conserving Power Dissipation with Shutdown

#### Connection for the Input Stage of SAR ADC

Most of the CMOS-based ADCs are integrated in microcontroller and have a sampling capacitor input structure. In addition, for charging the sampling capacitor of ADC, it needs the instantaneous charge from the output of the source. Adding an output capacitor ( $C_{FILT}$ ) can satisfy this requirement. For the size of  $C_{FILT}$ , it depends on the sampling frequency and the size of sampling capacitor. However, the input stages of the ADCs are not exactly the same, and thus the conditions of charge are also different. Figure 8 is just one example to show what the input stage of SAR ADC looks like.



Figure 8. Suitable Connection for the Input Stage of SAR ADC



### SGM449

## LAYOUT

#### Layout Guidelines

The SGM449 can be applied easily as other temperature sensors did, which can be glued or cemented on the surface. The difference between the sensing temperature and the actual temperature of the surface that the SGM449 be tied to is within 0.2°C.

However, the above presume is under the condition where the temperature of the air and the surface are equal. If the air temperature is changeable and its temperature is lower or higher than the surface which is closed to the SGM449, the calculated temperature is the average of both air and surface temperature. For enhancing the conductivity of the thermal, the backside of the die is connected to GND. The lands and traces are the parts of the PCB layout and also the temperature object of the SGM449.

Besides, the SGM449 can be installed inside a metal tube, or be screwed into a threaded hole. Also, the customer needs to be aware that the circuit and the external traces which are connected to the PCB board need to be kept dry enough and isolated, and this can prevent the device from leakage and corrosion, especially for the condensate conditions. The conformal coating and epoxy paints should be taken into account in order to avoid the connections in the PCB board from moisture.

### **REVISION HISTORY**

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Original (JUNE 2022) to REV.A	Page
Changed from product preview to production data	



# PACKAGE OUTLINE DIMENSIONS

## **SOT-23**





RECOMMENDED LAND PATTERN (Unit: mm)





Symbol	-	nsions meters	Dimensions In Inches		
	MIN	MAX	MIN	MAX	
A	0.89	1.12	0.035	0.044	
A1	0.01	0.10	0.000	0.004	
A2	0.88	1.02	0.035	0.040	
b	0.30 0.50		0.012	0.020	
С	0.08 0.20		0.003	0.008	
D	2.80	3.04	0.110	0.120	
E	1.20 1.40		0.047	0.055	
E1	2.10 2.64		0.083	0.104	
е	0.95	BSC	0.037	' BSC	
e1	1.90	BSC	0.075	5 BSC	
L	0.54	REF	0.021	REF	
L1	0.40	0.60	0.016	0.024	
θ	0° 8°		0°	8°	

NOTES:

1. Body dimensions do not include mode flash or protrusion.

2. This drawing is subject to change without notice.



## TAPE AND REEL INFORMATION

#### **REEL DIMENSIONS**



NOTE: The picture is only for reference. Please make the object as the standard.

#### KEY PARAMETER LIST OF TAPE AND REEL

Package Type	Reel Diameter	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P0 (mm)	P1 (mm)	P2 (mm)	W (mm)	Pin1 Quadrant
SOT-23	7″	9.5	3.15	2.77	1.22	4.0	4.0	2.0	8.0	Q3

### **CARTON BOX DIMENSIONS**



NOTE: The picture is only for reference. Please make the object as the standard.

### **KEY PARAMETER LIST OF CARTON BOX**

Reel Type	Length (mm)	Width (mm)	Height (mm)	Pizza/Carton	
7" (Option)	368	227	224	8	
7"	442	410	224	18	DD0002

