



拓展光电
TUOZHANGUANGDIAN

深圳市拓展光电有限公司

SHENZHEN DEVELOPMENT PHOTOELECTRIC CO., LTD

SPECIFICATION

Model: TZ5054UV365+395AS-011

Date: 2020/03/18

NO: SZTZ-DS-UVA-015

Par NO: F.50.00015

承制方确认

制作	审核	业务	品质

接受方确认

工程制定	工程审核	采购	品质



拓展光电
TUOZHANGUANGDIAN

制作	胡满意	日期	2021年03月18日
核准	魏峰	日期	2021年03月18日
版本号	A0	受控日期	2021年03月18日



TZ5054UVA365+395AS-011 Datasheet

The 5054 LED light source is a high-performance energy-saving device that can handle high heat and high drive current. Small size, high strength, is the ideal choice of LED nail lamp, LED mosquito lamp, The sterilization lamp, etc.

5054 LED光源是一种高性能节能器件。可在高热量和高驱动电流下工作。体积小、强度高，是LED指甲灯、LED诱蚊灯、杀菌灯等的理想选择。

The Purple LED light source with peak wavelength ranging from 365+395nm.

峰值波长为365+395nm的紫色LED光源。

This part has a footprint that is compatible to most of LEDs with similar size.

此器件可与大部份外形尺寸相似的LED兼容使用



FEATURES/特点




- 365+395nm dual peak wavelength
365+395nm双峰值波长
- High luminous Intensity and high efficiency
发光强度高，效率高
- Compatible with reflow soldering process
兼容回流焊工艺
- Low thermal resistance/热阻低
- Long operation life/寿命长
- Wide viewing angle at 120°
120° 发光角度
- Silicone encapsulation/硅胶封装
- Environmental friendly, RoHS compliance
材质环保，符合RoHS要求

APPLICATIONS/应用


- Nail lamp/指甲灯
- Mosquito lamp/诱蚊灯
- The sterilization lamp/杀菌灯



PACKAGE DIMENSIONS 封装尺寸



Recommended Solder Pad Design 推荐焊盘设计



Notes/注:

1. All dimensions in millimeters. 所有尺寸单位为mm
2. Thickness tolerance of copper plate is ± 0.02 mm. 铜材料片厚度公差为 ± 0.02 mm
3. Thickness tolerance of product is ± 0.05 mm. 产品厚度公差为 ± 0.05 mm
4. Tolerance is ± 0.1 mm unless otherwise noted. 如未特别注明， 默认公差为 ± 0.1 mm



ABSOLUTE MAXIMUM RATINGS最大限定参数 (Ta=25°C)

Parameter 项目名称	Symbol 符号	Value 规格	Unit 单位
Forward current 正向电流	I _F	80	mA
Peak Forward Current 正向脉冲电流	I _{FP}	100	mA
Reverse Voltage 反向电压	V _R	5	V
Power Dissipation 消耗功率	Pd	560	mW
Operating Temperature 工作温度	T _{opr}	-40~+85	°C
Storage Temperature 储存温度	T _{stg}	-40~+100	°C
Soldering Temperature 焊接温度	T _{sld}	Reflow Soldering: 260°C for 10 seconds	
LED Junction Temperature 结温	T _j	90	°C

CHARACTERISTICS 光电参数(Ta=25°C)


Parameter 项目名称	Symbol 单位	Condition 条件	Min 最小值	Typ 中间值	Max 最大值	Unit 单位
Reverse Current 反向漏电流	I _R	V _R =5V	--	--	3	uA
Forward Voltage 正向电压	V _F	I _F =80mA	6.8	7.0	7.2	V
Viewing Angle 发光角度	2θ _{1/2}	I _F =80mA	--	120	--	deg.
Radiant Flux 辐射通量	Φe	I _F =80mA	--	350	--	mW
peak wavelength 峰值波长	λP	I _F =80mA	365	--	375	nm
			390	--	400	nm
Thermal Resistance 热阻 (Junction to Solder Point)	R _{th-jS}	I _F =80mA	--	21	--	°C/W

Notes/注:


1. Radiant Flux is measured with an accuracy of ± 5%. 辐射功率的测量精度为± 5%。
2. peak wavelength is measured with an accuracy of ± 5%. 峰值波长的测量精度为± 5%。
3. All measurements were made under the standardized environment of Tuozhan
所有的测量都是在拓展的标准环境下进行的



RELATIVE SPECTRAL POWER DISTRIBUTION 相对光谱功率分布 ($T_j=25^\circ\text{C}$)




TYPICAL SPATIAL DISTRIBUTION 典型配光分布






RADIANT FIUX VS. CURRENT 辐射功率VS电流 ($T_j=25^\circ\text{C}$)

Radiant Flux vs Forward Current 辐射功率VS正向电流




ELECTRICAL CHARACTERISTICS 电特性($T_j=25^\circ\text{C}$)

Forward Current vs. Forward Voltage 正向电流VS正向电压






RADIANT FIUX VS. CURRENT 辐射功率VS电流 ($T_j=25^\circ\text{C}$)




ELECTRICAL CHARACTERISTICS 电特性($T_j=25^\circ\text{C}$)






CURRENT VS. AMBIENT TEMPERATURE 电流与环境温度



RELATIVE RADIANT FLUX VS. JUNCTION TEMPERATURE 结温VS相对辐射功率





SORTING RANKS 分光分级

(1) Radiant Flux 辐射功率($T_j=25^\circ\text{C}$)

Part Number 型号	Condition 条件	Rank 等级		Unit 单位
TZ5054UVA365+395AS-011	80mA	QC	QD	mW
		140-160	160-180	
		QE	RA	
		180-200	200-220	

(2) Forward Voltage 正向电压($T_j=25^\circ\text{C}$)

Rank 等级	Condition 条件	Min 最小值	Max 最大值	Unit 单位
DB	80mA	6.4	6.8	V
DC		6.8	7.2	
DD		7.2	7.6	

(3) peak wavelength 峰值波长

Part Number 型号	Condition 条件	Rank 等级		Unit 单位
TZ5054UVA365+395AS-011	80mA	CB	CC	nm
		365-370	370-375	
		CG	CH	
		390-395	395-400	
		DA	DB	
		400-405	405-410	

Notes/注:

1. 10% tolerance for luminous intensity may be caused by measurement inaccuracy.

光辐射功率测量精度误差 $\pm 5\%$

2. Measurement Uncertainty of the Forward Voltage : $\pm 0.05\text{V}$

正向电压测量误差: $\pm 0.05\text{V}$



REFLOW SOLDERING CHARACTERISTICS 回流焊特性

For Reflow Process 回流焊制程:

Preheating 预热: 140°C~160°C±5°C, within 2 minutes. 2分钟

Operation heating 作业加热: 260°C(Max.) within 10 seconds.(Max)

260°C(最高) within 10 seconds.(最长)

Gradual Cooling (Avoid quenching). 逐渐冷却(避免淬火)

Lead solder 有铅焊接	Lead-free solder 无铅焊接
Pre-heat 预热	120-150°C
Pre-heat time 预热时间	120 sec.Max.
Peak Temperature 峰值温度	240°C Max.
Soldering time condition 回流焊时间	10 sec.Max.

Lead Solder

2.5~5 °C / sec.

Pre-heating 120-150 °C

60sec. Max. Above 200 °C

240 °C Max. 10 sec. Max.

Lead-free Solder

1~5 °C / sec.

Pre-heating 150-200 °C


60sec. Max. Above 220 °C


260 °C Max. 10 sec. Max.

Notes注:

UV LED is using low-refractivity silicon glue, which is an extremely soft colloid. A suitable nozzle is required to pick the LED from lead frame body during the SMT process. If the nozzle is too small and contact with the LED surface, it may stick with the nozzle. It also may squeeze the silicon glue surface, which will cause wire deformation and lead to open-circuit defective, or dead LED after a long term usage.

UV LED使用低折硅胶，胶体极软。请选择合适的SMT吸嘴，吸取LED胶壳。如果吸嘴过小，吸嘴吸取LED胶面，有可能LED粘吸嘴，也有可能胶面被吸嘴挤压后，LED线材变形后开路不良，或者长期使用后死灯。





Notes注:

- (1) Quantity : 3,000pcs/Reel
数量: 3000pcs/卷
- (2) Cumulative Tolerance : Cumulative Tolerance/10 pitches to be $\pm 0.2\text{mm}$
累积公差: 累积公差/10间距 $\pm 0.2\text{毫米}$
- (3) Adhesion Strength of Cover Tape : Adhesion strength to be 0.1-0.7N when the cover tape is turned off from the carrier tape at the angle of 10° to the carrier tape
盖带粘附强度: 盖带反向拉, 与载带角度为10°, 拉力为0.1-0.7N
- (4) Package : P/N, Manufacturing data Code No. and quantity to be indicated on a damp proof Package.
包装: 品名, 生产数据代码和数量须在防潮包装上注明



Reliability Test Items 可靠性测试项目

Test Items 测试项目	Test Duration 测试时长	Number of Damaged 不良数
Steady State Operating Life of High Temperature (HTOL) Ts=85°C, IF=Max 高温点亮稳态老化Ts=85°C, IF=最大值	1000hrs	0/20
Steady State Operating Life of Low Temperature (LTOL) Ta=-40°C, IF=Max 低温点亮稳态老化Ts=85°C, IF=最大值	1000hrs	0/20
Pulse Wet Operating Life of High Temperature (PWHTOL) 高温高湿通断电老化 60°C/90%RH, IF30mins ON/30min OFF	500hrs	0/20
High Temperature Storage (HTS) 高温存储 100°C	1000hrs	0/20
Low Temperature Storage (LTS) 低温存储 -40°C	1000hrs	0/20
Thermal Shock (TS) -45°C~125°C 30min dwell 20sec transfer 冷热冲击-45°C 30min~125°C 30min , 转换时间20秒	300cycles	0/20
Solder Resistance (SR) 265°C, 3X MSL 阻焊测试 (3遍潮气敏感度试验后)	5sec	0/20
Solder Ability (SA) 245°C 5sec, 95% coverage 可焊性 95%覆盖	5sec	0/11
Mechanical Shock (MS) 1500G 0.5msec pulse shock 机械冲击(MS) 1500G 0.5毫秒脉冲冲击	Each 6 axis	0/6
Random Vibration (RV) 随机振动 6G RMS, 10-2000Hz, 10min	Per axis	0/6
Variable Vibration Frequency (VVF) 10-2000-10Hz, log or linear sweep rate, 20G for 1 min, 1.5mm each apply 3x per axis over 变频振动(VVF) 10-2000-10Hz, 对数或线性扫频, 20G, 1分钟, 1.5mm, 每轴3遍以上	6hrs	0/6
Salt Spread (SS) 35°C, 30g/m2/day 盐雾试验35°C,30克/平方米/天	48hrs	0/11

Item 项目	Symbol 符号	Test Condition 测试条件	Criteria for Judgment 判定标准	
			Min. 最小	Max. 最大
Forward Voltage 正向电压	V _F	IF=Typical Current 典型电流		U.S.L x1.1
Luminous Intensity 光功率	mW	IF=Typical Current	L.S.L x0.7	
peak wavelength 峰值波长	nm	IF=Typical Current		U.S.L x1.1



PRECAUTION FOR USE 使用注意事项

(1) This device should not be used in any type of fluid such as water, oil, organic solvent, etc.
When washing is required, IPA should be used.

本器件不得用于水、油、有机溶剂等任何流体中。如需清洁，请使用异丙醇进行清洗。

(2) When the LEDs are illuminating, operating current should be decided after considering the ambient maximum temperature.

当LED发光工作时，应根据环境最高温度来确定工作电流。

(3) LEDs must be stored to maintain a clean atmosphere. If the LEDs are stored for 3months or more after being shipped from TuoZhan, a sealed container with a nitrogen atmosphere should be used for storage.

LED储存环境须保持清洁。如果LED从拓展发货后需储存3个月或更长时间，则应使用氮气柜进行储存。

(4) The LEDs must be used within seven days after opening the moisture proof packing.

Rewrap unused Products with anti-moisture packing, fold to close any opening and then store in a dry place.

LED须在打开防潮包装后七天内使用。用防潮包装重新包装未使用的产品，折叠以封住开口，然后存放在干燥的地方。

(5) The appearance and specifications of the product may be modified for improvement without notice.

产品外观及规格如有改进，恕不另行通知。

(6) This LED is sensitive to the static electricity and surge. It is recommended to use a wrist Band or anti-electrostatic glove when handling the LEDs.

LED对静电和浪涌很敏感。在处理LED时，建议使用防静电腕带或防静电手套。

(7) On manual soldering, a solder tip must be needed as grounded for usage. If over voltage which exceeds the absolute maximum rating is applied to LEDs, it will cause damage LEDs and result in destruction. Damaged LEDs will show some unusual characteristics such as leak current remarkably increase ,turn-on voltage becomes lower and the LEDs get unlighted at low current.

手工焊接时，焊接头必须接地。如果对led施加超过绝对最大额定值的过电压，会对led造成损坏。损坏的led会出现一些不寻常的特性，如漏电流明显增加，接通电压降低，低电流时led不亮。

(8) Warm prompt "The UV damage eyes, Do not stare at the light source, And don't shine a light into someone's eyes"

温馨提示：“UV伤眼！不要盯着光源看，也不要用光源照射别人的眼睛！”

