



ITEM	XRRH 3.5*6.0*0.8TAPING
PART NO.	
ELECTRICAL REQUIREMENTS	IMPEDANCE Z:60 MIN OHM(100MHZ)

TEST MEHOD

APPEARANCE STANDARD	VISION
INSPECTION LEVEL	MIL-SID-105D AQL=0.1
CHARACT&SIZE	LEVEL S-3
SURFACE	LEVEL II
TEST EQUIPMENT	HP-4191A
TEST FREQUENCY	100MHZ
COIL SPEC	

DIMENSION

(UNIT:mm)



$$A=3.50\pm 0.20\text{m/m}$$

$$C=0.80\pm 0.20\text{m/m}$$

$$D=6.00\pm 0.20\text{m/m}$$



ITEM	XRRH 3.5*6.0*0.8TAPING
PART NO.	

PACKAGING

Available in tape and reel bulk


TAPE DIMENSION:

TYPE	B	E	F	H	I	J	P	d1-d2
XRRH3.5*6.0*0.8	63.00	6.00	52.2	4.20	1.35	0.80	5.00	1.20
	±3.00	±0.50	±1.50	MIN	MAX	MAX	±0.50	MAX




TEST DATA

CUSTOMER				QUANTITY						
ITEM	XRRH 3.5*6.0*0.8 TAPING			COIL SPEC						
PART NO.				TEST FREQUENCY	100MHZ					
HUMIDITY	63%			TEST EQUIPMENT	HP-4191A					
TEMPERATURE	23°C									
	TESTRESOLUTION			DIMENSION(UNIT:mm)						
	Z MHZ	Z MHZ	Z 100MHZ	A	B	C	D	E	F	
SPEC	Ω MIN	Ω MIN	60Ω MIN	3.50 ±0.20		0.80 ±0.20	6.00 ±0.20			
1			78	3.51		0.80	5.98			
2			76	3.50		0.85	6.00			
3			78	3.48		0.88	6.00			
4			81	3.56		0.90	6.01			
5			80	3.50		0.98	6.01			
6										
7										
8										
9										
10										
MEAN										
R										



ITEM: XRRH 3.5*6.0*0.8 TAPING



METER: HP-4191A