

■ Features

- Ultra low profile.
- Magnetic shielded for low radiation.
- Bobbin ferrite core and compact size.
- Low core loss for high frequency power application.
- Large terminal surface for good PCB bonding.
- Operating temperature:-40℃ ~ +125℃.

■ Applications

- Portable communication equipment.
- Notebook PC,digital camera,LCD television set.
- Power supply for VTR,OA equipment.
- DC/DC converters.

■ Product Identification

$\frac{\text{XRRH}}{(1)} \quad \frac{\square\square\square\square}{(2)} - \frac{\square\square\square}{(3)} \quad \frac{\text{M}}{(4)}$


(1) : Type

(2) : Dimensions

(3) : Inductance value

(4) : Inductance Tolerance; N=±30%,M=±20%, K=±10%

■ Shapes and Dimensions (Unit: mm)



TYPE	A	B	C max.	D	E	F Ref.	G Ref.	H Ref.
XRRH2D18	3.2±0.3	3.2±0.3	2.0	1.15	4.5	1.2	1.0	2.9

■ XRRH3D16 Series


Part Number	Inductance (uH)	Test Freq.(KHz)	DCR MAX.(Ω)	Rated Current (A)
XRRH2D18-2R2M	2.2	100	0.041	2.00
XRRH2D18-3R3M	3.3	100	0.054	1.80
XRRH2D18-4R7M	4.7	100	0.078	1.40
XRRH2D18-6R8M	6.8	100	0.106	1.07
XRRH2D18-100M	10.0	100	0.180	0.75
XRRH2D18-150M	15.0	100	0.220	0.55
XRRH2D18-220M	22.0	100	0.320	0.42
XRRH2D18-330M	33.0	100	0.460	0.38
XRRH2D18-470M	47.0	100	0.660	0.33

※ The saturation current value is the DC current value having inductance decrease down to 30%.(at 20℃)

※ The temperature rise current value is the DC current value having temperature increase up to 40℃. (at 20℃)


※ The rated current is the DC current value that satisfies both of current value saturation current value and temperature rise current value.

■ Taping Dimensions(Unit:mm)




TYPE	W	A	B	C	D	E	P	K Ref	T	MPQ
XRRH2D18	12±0.3	4.35±0.1	4.35±0.1	4.75	5.5±0.1	2.10±0.1	8.0±0.1	2.30	0.40±0.05	3500

■ Reel Dimensions(Unit:mm)




TYPE	W	W1	W2	W3	A	B	C	D
XRRH2D18	330±2.0	12.4±2.0	13.5MAX	11.9 Min	13.0±0.50	21.0±0.80	2.0±0.50	100 Min

■ Direction of rolling



■ Cover tape peel off condition



Cover tape peel force shall be 0.1N to 1.3N.

Reference peel speed 300 ± 10 mm/min.