

ISL2100A, ISL2101A

100V, 2A Peak, High Frequency Half-Bridge Drivers

FN6294 Rev 4.1 Jul 22, 2021

The ISL2100A, ISL2101A are 100V, high frequency, half-bridge N-channel power MOSFET driver ICs. They are based on the popular HIP2100, HIP2101 half-bridge drivers, but offer several performance improvements. The ISL2100A has additional input hysteresis for superior operation in noisy environments and the inputs of the ISL2101A, like those of the ISL2100A, can now safely swing to the V_{DD} supply rail. Finally, both parts are available in a very compact 9 Ld DFN package to minimize the required PCB footprint


Applications

- Telecom Half-Bridge Converters
- · Telecom Full-Bridge Converters
- · Two-Switch Forward Converters
- · Active-Clamp Forward Converters
- · Class-D Audio Amplifiers

Features


- · Drives N-Channel MOSFET Half-Bridge
- · Space-Saving DFN Package
- DFN Package Compliant with 100V Conductor Spacing Guidelines per IPC-2221
- · Pb-Free (RoHS compliant)
- Bootstrap Supply Max Voltage to 114V_{DC}
- On-Chip 1Ω Bootstrap Diode
- Fast Propagation Times for Multi-MHz Circuits
- · Drives 1nF Load with Typical Rise/Fall Times of 10ns
- CMOS Compatible Input Thresholds (ISL2100A)
- 3.3V/TTL Compatible Input Thresholds (ISL2101A)
- · Independent Inputs Provide Flexibility
- · No Start-Up Problems
- Outputs Unaffected by Supply Glitches, HS Ringing Below Ground or HS Slewing at High dv/dt
- · Low Power Consumption
- Wide Supply Voltage Range (9V to 14V)
- · Supply Undervoltage Protection
- 2.5Ω Typical Output Pull-Up/Pull-Down Resistance

Application Block Diagram





Functional Block Diagram



*EPAD = EXPOSED PAD. THE EPAD IS ELECTRICALLY ISOLATED FROM ALL OTHER PINS. FOR BEST THERMAL PERFORMANCE CONNECT THE EPAD TO THE PCB POWER GROUND PLANE.




FIGURE 1. TWO-SWITCH FORWARD CONVERTER




FIGURE 2. FORWARD CONVERTER WITH AN ACTIVE-CLAMP


Ordering Information

PART NUMBER (Note)	PART MARKING	PACKAGE DESCRIPTION (RoHS Compliant)	PKG. DWG.#	CARRIER TYPE (Note 1)	TEMP. RANGE
ISL2100AAR3Z	00AZ	9 Ld 3x3 DFN	L9.3x3	Tube	-40 to +125°C
ISL2100AAR3Z-T	-			Reel, 6k	
ISL2101AAR3Z	01AZ			Tube	
ISL2101AAR3Z-T				Reel, 6k	
ISL2101AABZ	01ABZ	8 Ld SOIC	M8.15	Tube	
ISL2101AABZ-T				Reel, 2.5k	

NOTES:

- 1. See TB347 for details on reel specifications.
- 2. These Pb-free plastic packaged products employ special Pb-free material sets, molding compounds/die attach materials, and 100% matte tin plate plus anneal (e3 termination finish, which is RoHS compliant and compatible with both SnPb and Pb-free soldering operations). Pb-free products are MSL classified at Pb-free peak reflow temperatures that meet or exceed the Pb-free requirements of IPC/JEDEC J STD-020.
- 3. For Moisture Sensitivity Level (MSL), see the ISL2100A and ISL2101A device pages. For more information about MSL, see TB363.

Pinouts



Pin Descriptions

SYMBOL	DESCRIPTION
V_{DD}	Positive supply to lower gate driver. Bypass this pin to V _{SS} .
НВ	High-side bootstrap supply. External bootstrap capacitor is required. Connect positive side of bootstrap capacitor to this pin. Bootstrap diode is on-chip.
НО	High-side output. Connect to gate of high-side power MOSFET.
HS	High-side source connection. Connect to source of high-side power MOSFET. Connect negative side of bootstrap capacitor to this pin.
HI	High-side input.
LI	Low-side input.
V _{SS}	Chip negative supply, which will generally be ground.
LO	Low-side output. Connect to gate of low-side power MOSFET.
EPAD	Exposed pad. Connect to ground or float. The EPAD is electrically isolated from all other pins.



Absolute Maximum Ratings

Supply Voltage, V _{DD} , V _{HB} - V _{HS} (Notes <u>4</u> , <u>5</u>)0.3V to 18V
LI and HI Voltages (Note <u>5</u>)0.3V to V _{DD} + 0.3V
Voltage on LO (Note <u>5</u>)0.3V to V _{DD} + 0.3V
Voltage on HO (Note <u>5</u>) V _{HS} - 0.3V to V _{HB} + 0.3V
Voltage on HS (Continuous) (Note 5)1V to 110V
Voltage on HB (Note <u>5</u>)
Average Current in V _{DD} to HB Diode

Thermal Information

Thermal Resistance (Typical)	θ _{JA} (°C/W)	θ _{JC} (°C/W)
DFN (Notes <u>6</u> , <u>7</u>)	47	3.5
SOIC (Notes <u>8</u> , <u>9</u>)	107	50
Max Power Dissipation at +25°C in Free Ai	r (DFN, Note	<u>6</u>) 2.27W
Storage Temperature Range	-65 °	°C to +150°C
Pb-Free Reflow Profile		. see <u>TB493</u>

Maximum Recommended Operating Conditions

Supply Voltage, V _{DD}	9V to 14V
Voltage on HS	1V to 100V
Voltage on HS	(Repetitive Transient) -5V to 105V
Voltage on HB V _{HS} + 8V to V _{HS}	+ 14V and V _{DD} - 1V to V _{DD} + 100V
HS Slew Rate	<50V/ns

CAUTION: Do not operate at or near the maximum ratings listed for extended periods of time. Exposure to such conditions may adversely impact product reliability and result in failures not covered by warranty.

NOTES:

- 4. The ISL2100A-ISL2101A are capable of derated operation at supply voltages exceeding 14V. Figure 22 shows the high-side voltage derating curve for this mode of operation.
- 5. All voltages referenced to $V_{\mbox{SS}}$ unless otherwise specified.
- 6. θ_{JA} is measured in free air with the component mounted on a high effective thermal conductivity test board with "direct attach" features.
- 7. For θ_{JC} , the case temperature is measured at the center of the exposed metal pad on the package underside. See <u>TB379</u> for details.
- 8. θ_{JA} is measured in free air with the component mounted on a high-effective thermal conductivity test board.
- 9. For θ_{JC_i} the case temperature is measured at the center top of the package. See <u>TB379</u> for details.

Electrical Specifications V_{DD} = V_{HB} = 12V, V_{SS} = V_{HS} = 0V, No Load on LO or HO, Unless Otherwise Specified. Parameters with MIN and/or MAX limits are 100% tested at +25°C, unless otherwise specified. Temperature limits established by characterization and are not production tested.

			T _J = +25°C		T _J = -40°C to +125°C			
PARAMETERS	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	MIN	MAX	UNITS
SUPPLY CURRENTS								
V _{DD} Quiescent Current	I _{DD}	ISL2100A; LI = HI = 0V	-	0.1	0.25	-	0.3	mA
V _{DD} Quiescent Current	I _{DD}	ISL2101A; LI = HI = 0V	-	0.3	0.45	-	0.55	mA
V _{DD} Operating Current	I _{DDO}	ISL2100A; f = 500kHz	-	1.6	2.2	-	2.7	mA
V _{DD} Operating Current	I _{DDO}	ISL2101A; f = 500kHz	-	1.9	2.5	-	3	mA
Total HB Quiescent Current	I _{HB}	LI = HI = 0V	-	0.1	0.15	-	0.2	mA
Total HB Operating Current	Інво	f = 500kHz	-	2.0	2.5	-	3	mA
HB to V _{SS} Current, Quiescent	I _{HBS}	LI = HI = 0V; V _{HB} = V _{HS} = 114V	-	0.05	1	-	10	μΑ
HB to V _{SS} Current, Operating	I _{HBSO}	f = 500kHz; V _{HB} = V _{HS} = 114V	-	0.9	-	-	-	mA
INPUT PINS					•			
Low Level Input Voltage Threshold	V _{IL}	ISL2100A	3.7	4.4	-	2.7	-	V
Low Level Input Voltage Threshold	V _{IL}	ISL2101A	1.4	1.8	-	1.2	-	V
High Level Input Voltage Threshold	V _{IH}	ISL2100A	-	6.6	7.4	-	8.4	V
High Level Input Voltage Threshold	V _{IH}	ISL2101A	-	1.8	2.2	-	2.4	V
Input Voltage Hysteresis	V _{IHYS}	ISL2100A	-	2.2	-	-	-	V
Input Pull-down Resistance	R _I		-	210	-	100	500	kΩ
UNDERVOLTAGE PROTECTION	1	1		1			1	1
V _{DD} Rising Threshold	V_{DDR}		6.8	7.3	7.8	6.5	8.1	V



Electrical Specifications $V_{DD} = V_{HB} = 12V$, $V_{SS} = V_{HS} = 0V$, No Load on LO or HO, Unless Otherwise Specified. Parameters with MIN and/or MAX limits are 100% tested at +25°C, unless otherwise specified. Temperature limits established by characterization and are not production tested. **(Continued)**

			T _J = +25°C			T _J = -40°C to +125°C		
PARAMETERS	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	MIN	MAX	UNITS
V _{DD} Threshold Hysteresis	V _{DDH}		-	0.6	-	-	-	V
HB Rising Threshold	V _{HBR}		6.2	6.9	7.5	5.9	7.8	V
HB Threshold Hysteresis	V _{HBH}		-	0.6	-	-	-	V
BOOTSTRAP DIODE			·					
Low Current Forward Voltage	V _{DL}	I _{VDD-HB} = 100μA	-	0.5	0.6	-	0.7	V
High Current Forward Voltage	V _{DH}	I _{VDD-HB} = 100mA	-	0.7	0.9	-	1	V
Dynamic Resistance	R _D	I _{VDD-HB} = 100mA	-	8.0	1	-	1.5	Ω
LO GATE DRIVER								
Low Level Output Voltage	V _{OLL}	I _{LO} = 100mA	-	0.25	0.3	-	0.4	V
High Level Output Voltage	V _{OHL}	I _{LO} = -100mA, V _{OHL} = V _{DD} - V _{LO}	-	0.25	0.3	-	0.4	V
Peak Pull-Up Current	I _{OHL}	V _{LO} = 0V	-	2	-	-	-	Α
Peak Pull-Down Current	l _{OLL}	V _{LO} = 12V	-	2	-	-	-	Α
HO GATE DRIVER								
Low Level Output Voltage	V _{OLH}	I _{HO} = 100mA	-	0.25	0.3	-	0.4	V
High Level Output Voltage	V _{ОНН}	I _{HO} = -100mA, V _{OHH} = V _{HB} - V _{HO}	-	0.25	0.3	-	0.4	V
Peak Pull-Up Current	Гонн	V _{HO} = 0V	-	2	-	-	-	Α
Peak Pull-Down Current	l _{OLH}	V _{HO} = 12V	-	2	-	-	-	Α

Electrical Specifications Switching Specifications V_{DD} = V_{HB} = 12V, V_{SS} = V_{HS} = 0V, No Load on LO or HO, Unless Otherwise Specified. Parameters with MIN and/or MAX limits are 100% tested at +25°C, unless otherwise specified. Temperature limits established by characterization and are not production tested.

		TEST	T _J = +25°C			T _J = -40°C to +125°C		
PARAMETERS	SYMBOL	CONDITIONS	MIN	TYP	MAX	MIN	MAX	UNITS
Lower Turn-Off Propagation Delay (LI Falling to LO Falling)	tLPHL		-	34	50	-	60	ns
Upper Turn-Off Propagation Delay (HI Falling to HO Falling)	t _{HPHL}		-	31	50	-	60	ns
Lower Turn-On Propagation Delay (LI Rising to LO Rising)	t _{LPLH}		-	39	50	-	60	ns
Upper Turn-On Propagation Delay (HI Rising to HO Rising)	tHPLH		-	39	50	-	60	ns
Delay Matching: Upper Turn-Off to Lower Turn-On	t _{MON}		1	8	-	-	16	ns
Delay Matching: Lower Turn-Off to Upper Turn-On	t _{MOFF}		1	6	-	-	16	ns
Either Output Rise/Fall Time (10% to 90%/90% to 10%)	t _{RC,} t _{FC}	C _L = 1nF	-	10	-	-	-	ns
Either Output Rise/Fall Time (3V to 9V/9V to 3V)	t_{R,t_F}	C _L = 0.1µF	-	0.5	0.6	-	8.0	us
Minimum Input Pulse Width that Changes the Output	t _{PW}		-	-	-	-	50	ns
Bootstrap Diode Turn-On or Turn-Off Time	t _{BS}		-	10	-	-	-	ns

Timing Diagrams




FIGURE 3. PROPAGATION DELAYS




FIGURE 4. DELAY MATCHING

Typical Performance Curves




FIGURE 5. ISL2100A IDD OPERATING CURRENT vs FREQUENCY




FIGURE 6. ISL2101A IDD OPERATING CURRENT vs FREQUENCY




FIGURE 7. IHB OPERATING CURRENT vs FREQUENCY




FIGURE 8. IHBS OPERATING CURRENT vs FREQUENCY

Typical Performance Curves (Continued)




FIGURE 9. HIGH LEVEL OUTPUT VOLTAGE vs TEMPERATURE




FIGURE 10. LOW LEVEL OUTPUT VOLTAGE vs TEMPERATURE




FIGURE 11. UNDERVOLTAGE LOCKOUT THRESHOLD vs TEMPERATURE




FIGURE 12. UNDERVOLTAGE LOCKOUT HYSTERESIS vs TEMPERATURE




FIGURE 13. ISL2100A PROPAGATION DELAYS vs TEMPERATURE




FIGURE 14. ISL2101A PROPAGATION DELAYS vs TEMPERATURE

Typical Performance Curves (Continued)




FIGURE 15. ISL2100A DELAY MATCHING vs TEMPERATURE




FIGURE 16. ISL2101A DELAY MATCHING vs TEMPERATURE




FIGURE 17. PEAK PULL-UP CURRENT vs OUTPUT VOLTAGE




FIGURE 18. PEAK PULL-DOWN CURRENT vs OUTPUT VOLTAGE




FIGURE 19. ISL2100A QUIESCENT CURRENT vs VOLTAGE




FIGURE 20. ISL2101A QUIESCENT CURRENT vs VOLTAGE

Typical Performance Curves (Continued)




FIGURE 21. BOOTSTRAP DIODE I-V CHARACTERISTICS




FIGURE 22. VHS VOLTAGE vs $V_{\mbox{\scriptsize DD}}$ VOLTAGE

Revision History


The revision history provided is for informational purposes only and is believed to be accurate, but not warranted. Please go to the web to make sure that you have the latest revision.


DATE	REVISION	CHANGE
Jul 22, 2021	4.1	Updated external links throughout. Updating Ordering Information table format, removed retired part, corrected typo for SOIC package. Updated SOIC Thermal Information as follows: -Changed Theta JA from 120 to 107 -Changed Theta JC from N/A to 50 -Added Notes 8 and 9 and referenced them to SOIC thermals. Removed About Intersil Updated POD L9.3x3 to the latest revision, changes are as follows: -Updated to new format with dimensions included. Also added a PCB land pattern. Added latest version of POD M8.15.
Dec 8, 2015	4.0	- Updated Ordering Information Table on page 3. - Added Revision History. - Added About Intersil Verbiage. - Updated POD L9.3X3 to latest revision changes are as follow: Tiebar shown (if present) is a non-functional feature and may be located on any of the 4 sides (or ends) - Updated POD M8.15 to latest revision changes are as follow: Changed Note 1 "1982" to "1994" Changed in Typical Recommended Land Pattern the following: 2.41(0.095) to 2.20(0.087) 0.76 (0.030) to 0.60(0.023) 0.200 to 5.20(0.205) Updated to new POD format by removing table and moving dimensions onto drawing and adding land pattern.


Package Outline Drawings

For the most recent package outline drawing, see <u>L9.3x3</u>.


L9.3x3 9 Lead Dual Flat No-Lead Plastic Package (DFN) Rev 2, 4/20







Typical Recommended Land Pattern




Bottom View

- Dimensions are in millimeters.
 Dimensions in () for reference only.
- 2. Dimensioning and tolerancing conform to ASME Y14.5m-1994.
- 3. Unless otherwise specified, tolerance: Decimal ±0.05
- This dimension applies to the metallized terminal and is measured between 0.15mm and 0.30mm from the terminal tip.
- Tiebar shown (if present) is a non-functional feature.
- The configuration of the pin #1 identifier is optional, but must be located within the zone indicated. The pin #1 identifier can be either a mold or mark feature.

For the most recent package outline drawing, see M8.15.

M8.15

8 Lead Narrow Body Small Outline Plastic Package Rev 5, 4/2021



NOTES:

- 1 Dimensioning and tolerancing conform to AMSEY14.5m-1994.
- 2 Package length does not include mold flash, protrustion or gate burrs. Mold flash, protrustion and gate burrs shall not exceed 0.15mm (0.006 lnch) per side.
- 3. Package width does not include interlead flash or protrustions. Interlead flash and protrustions shallnot exceed 0.25mm (0.010 inch) per side.
- 4. The chamfer on the body is optional. If it is not present, a visual index feature must be located within the crosshatched area.
- 5 Terminal numbers are shown for reference only.
- 6 The lead width as measured 0.36mm (0.014 inch) or greater above the seating plane, shall not exceed a maximum value of 0.61mm (0.024 inch).
- 7 Controlling dimension: MILLIMETER. Converted inch dimension are not necessarily exact.
- 8 This outline conforms to JEDEC publication MS-012-AA ISSUE C.

IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES ("RENESAS") PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers skilled in the art designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only for development of an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising out of your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Rev.1.0 Mar 2020)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu, Koto-ku, Tokyo 135-0061, Japan www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:

www.renesas.com/contact/