


Features

- Low profile space
- Ideal for automated placement
- Glass passivated chip junction
- Low forward voltage drop
- Low leakage current
- High forward surge capability
- High temperature soldering:
260°C/10 seconds at terminals



Dimensions in millimeters and (inches)

Maximum Ratings & Thermal Characteristics $(T_A = 25^\circ C$ unless otherwise noted)

Items	Symbol	UMB 05F	UMB 1F	UMB 2F	UMB 4F	UMB 6F	UMB 8F	UMB 10F	UNIT
Maximum repetitive peak reverse voltage	V_{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V_{RMS}	35	70	140	280	420	560	700	V
Maximum DC blocking voltage	V_{DC}	50	100	200	400	600	800	1000	V
Maximum average forward rectified current at $T_A=50^\circ C$ -on glass-epoxy P.C.B. ⁽¹⁾ at $T_A=30^\circ C$ -on aluminum substrate ⁽²⁾	$I_{F(AV)}$					0.5	0.8		A
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load (JEDEC Method)	I_{FSM}					20			A
Thermal resistance from junction to ambient per leg	$R_{\theta JA}^{(1)}$ $R_{\theta JA}^{(2)}$				100	80			°C/W
Thermal resistance from junction to lead per leg ⁽¹⁾	$R_{\theta JL}$				30				°C/W
Operating junction and storage temperature range	T_J, T_{STG}				-55 to +150				°C

Note 1: On glass epoxy P.C.B. mounted on 0.05×0.05" (1.3×1.3mm) pads

Note 2: On aluminum substrate P.C.B. with an area of 0.8×0.8" (20×20mm) mounted on 0.05×0.05" (1.3×1.3mm) solder pad

Electrical Characteristics $(T_A = 25^\circ C$ unless otherwise noted)

Items	Test conditions		Symbol	Min	Type	Max	UNIT
Instantaneous forward voltage per leg	$I_F=0.4A^{(3)}$		V_F	-	0.96	1.10	V
Reverse current per leg us pulse width.1% duty cycle.	$V_R=V_{DC}$	$T_J=25^\circ C$ $T_J=125^\circ C$	I_R	-	-	5 100	µA

Note 3: Pulse test:300

Characteristic Curves ($T_A=25^\circ\text{C}$ unless otherwise noted)

Fig.1 Forward Current Derating Curve




Fig.2 Maximum Non-Repetitive Peak Forward Surge Current




Fig.3 Typical Instantaneous Forward Characteristics





Fig.4 Typical Reverse Leakage Characteristics



Marking

Annotation of Marking Code:

Device Type	Device Marking
UMB05F	B1
UMB1F	B2
UMB2F	B3
UMB4F	B4
UMB6F	B5
UMB8F	B6
UMB10F	B7