




REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	BATCH PRODUCTION INITIAL RELEASE.	2015.06.26	邱國強



Specifications  
 Current Rating:2.0Amp  
 Insulation Resistance:1000MΩMin.  
 Dielectric Withstanding Voltage:500VAC  
 Contact Resistance:20mΩMax.  
 Operating Temperature:-40°C to +105°C  
 Materials  
 Contact Material:Brass  
 Insulator Material:High Temperature Thermoplastic, UL 94V-0 Nylon 6T (Halogen Free)or the equivalent material  
 All materials must meet Greenconn hazardous substances control standards.

### Ordering Information


G PFA104 - XX XX A 060 R 1 B X

No. of Pins per Row 02~40  
 Standard Plating 02=Gold Flash  
 Selective Plating 01=Tin  
 05=Gold Flash/Tin

Color 1=Black

Standard Packing A=Box  
 Selective Packing C=Tube

Recommended P.C.Board Layout  
 (Tolerance:±0.05)



格菱股份有限公司  
**Greenconn Corporation**

GENERAL TOLERANCE		DESIGNED: 邱國強	DATE: 2015.06.26	DWG. NO.	TITLE. 2.00 PIN HEADER SINGLE ROW DIP TYPE CONNECTOR
X.*±5.0°	X.±0.30	CHECKED:	DATE:	GPFA104-CA60RB	
.X*±3.0°	.X±0.25	CO SIGNED: 楊明勝	DATE: 2015.06.26	PART NO.	
.XX*±2.0°	.XX±0.15	APPROVED:	DATE:	GPFA104-XXXX A060R1BX	
.XXX*±1.0°	.XXX±0.10				