





REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
A	NEW	INTERIM INITIAL RELEASE.	2022.12.29	郭 康



Specifications
Current Rating:2.0Amp
Insulation Resistance:1000MΩMin.
Dielectric Withstanding Voltage:500VAC
Contact Resistance:20mΩMax.
Operating Temperature:-40°C to +105°C
Materials
Contact Material:Copper alloy
High Temperture Thermoplastic: Suitable for
Reflow Soldering Process (LCP, Nylon
10T,NYLON-HTN)
All materials must meet Greenconn
hazardous substances control standards.

Recommended P.C.Board
Layout
(Tolerance:±0.05)



Ordering Information

G PFA301 - XX XX A 008 X X X X

No. of Pins per Row 02~40
Standard Plating 02=Gold Flash
Selective Plating 05=Gold Flash/Tin
01=Tin
Insulator Material Y=NYLON-10T
C=LCP
R=NYLON-HTN
Color 1=Black
5=Natural
Contact Material A=Phosphor Bronze
B=Brass
Standard Packing C=Tube(04~40PIN)
Selective Packing A=Box
E=Cap+Tube(04~40PIN)
F=Cap+Tape&Reel
D=Tape&Reel



3RD.ANG
PROJ.
PAGE. 1/1

GENERAL TOLERANCE	
X.*±5.0°	X.±0.30
.X*±3.0°	.X±0.25
.XX*±2.0°	.XX±0.15
.XXX*±1.0°	.XXX±0.10

DESIGNED: 郭 康
DATE: 2022.12.29
CHECKED: 張春進
DATE: 2022.12.29
APPROVED: 張春進
DATE: 2022.12.29

DWG. NO.
GPFA301-CA008
PART NO.
GPFA301-XXXX A008XXXX

TITLE.
2.00 PIN HEADER
THREE ROWS DIP TYPE
CONNECTOR