





REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	INITIAL RELEASE.	2006.03.20	皮洪斌
02	△	變更料號	2008.10.07	彭思城
03	△	變更圖號	2012.03.27	黃小燕



Specifications
 Current Rating: 2Amp
 Insulation Resistance: 1000MΩMin.
 Dielectric Withstanding Voltage: 500VAC
 Contact Resistance: 20mΩMax.
 Operating Temperature: -40°C to +105°C
 Materials
 Contact Material: Brass
 Insulator Material: Thermoplastic, UL 94V-0 PBT or the equivalent material
 All materials must meet Greenconn requirement for environment protection.

Recommended P.C.Board Layout
 (Tolerance: ±0.05)



Ordering Information

G PFA201 - XX XX A 105 A 1 B X

No. of Pins per Row 02~40
 Standard Plating 02=Gold Flash
 Selective Plating 01=Tin 05=Gold Flash/Tin
 Color 1=Black
 Standard Packing A=box
 Selective Packing C=Tube

格稜股份有限公司
Greenconn Corporation

GENERAL TOLERANCE	
X. ± 5.0°	X. ± 0.30
.X ± 3.0°	.X ± 0.25
.XX ± 2.0°	.XX ± 0.15
.XXX ± 1.0°	.XXX ± 0.10

DESIGN: 黃小燕
 CHECKED: 劉北平
 AUDITED: 李輝
 APPROVED: cc_li

DATE: 2012.03.27
 DATE: 2012.03.27
 DATE: 2012.03.27
 DATE: 2012.03.27

DWG. NO. △ GPFA201-CA105AB
 PART NO. △ GPFA201-XXXX A105A1BX

TITLE:
 2.00 PIN HEADER
 DUAL ROWS DIP TYPE
 BASE 2.00H

REV.	UNIT.	SCALE.	PAGE.
03	mm	4:1	1/1