REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	BATCH PRODUCTION INITIAL RELEASE.	2013.01.24	邱明周
02	△02	依業務要求變更產品平整度	2017.04.17	馮國東



Dim.C	NOTE
4.00	02PIN
5.00	03~08PIN
8.16	09~40PIN

Specifications
Current Rating:2.0Amp
Insulation Resistance:1000MΩMin.
Dielectric Withstanding Voltage:500VAC
Contact Resistance:20mΩMax.
Operating Temperature:−40°C to +105°C
Materials
Contact Material:Brass
Insulator Material:High Temperature Thermoplastic, UL 94V−0 LCP or the equivalent material
All materials must meet Greenconn hazardous substances control standards.





Recommended P.C.Board Layout
(Tolerance:±0.05)



Ordering Information

G PFC217 − XX XX A 023 C 1 B X

- XX: No. of Pins per Row 02~40
- XX: Standard Plating 02=Gold Flash; Selective Plating 01=Tin, 05=Gold Flash/Tin
- A: Color 1=Black
- B: Standard Packing C=Tube; Selective Packing A=Box, E=CAP+Tube, F=CAP+Tape&Reel
- X: (blank)

△02

Dim.D	NOTE
0.12	02~09PIN
0.15	10~40PIN

格稜股份有限公司 Greenconn Corporation				
REV. 02	UNIT. mm	SCALE. 5:1	PAGE. 1/1	

GENERAL TOLERANCE	
X.°±5.0°	X.±0.30
.X°±3.0°	.X±0.25
.XX°±2.0°	.XX±0.15
.XXX°±1.0°	.XXX±0.10

DESIGNED: 馮國東	DATE: 2017.04.17
CHECKED: 曹 熙	DATE: 2017.04.17
CO SIGNED: 劉北平	DATE: 2017.04.17
APPROVED: 李 輝	DATE: 2017.04.17

DWG. NO. GPFC217−CA23CB

PART NO. GPFC217−XXXX A023C1BX

TITLE. 2.00 PIN HEADER DUAL ROWS SMT TYPE CONNECTOR