



### Product Summary


- -2.3A,-8V
- RDS(ON)=55mΩ @ VGS=4.5V(Typ)
- RDS(ON)=65mΩ @ VGS=2.5V(Typ)
- FDC6331L Pin to Pin fully compatible

### Application

- Battery Packs
- Battery-Powered Portable Equipment
- Cellular and Cordless Telephones


### Package and Pin Configuration

**SOT23-6**



**Marking: 323K**


**Circuit diagram**



### Absolute Maximum Ratings ( $T_A=25^\circ\text{C}$ unless otherwise noted)


Symbol	Parameter	Limit	Unit
$V_{IN}$	Input Voltage	3-8	V
$V_{ON/OFF}$	ON/OFF Voltage	-1.5 to 8	
$I_L$	Continuous Load Current	-2.3	A
	Pulse Load Current	-5	
$I_S$	Continuous Source Current (Source-Drain Diode)	-1.0	
$P_D$	Maximum Power Dissipation	0.7	
$T_J, T_{STG}$	Junction and Storage Temperature Range	-50 to +150	°C
ESD	ESD Rating, MIL-STD-883D HBM	2000	V
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	250	°C/W

**Typical Application Circuit**



<b>COMPONENTS</b>		
R1	Pull-Up Resistor	Typical 20kΩ to 1MΩ*
R2	Optional Slew-Rate Control	Typical 0 to 50kΩ
C1	Optional Slew-Rate Control	Typical 1000pF

\*Minimum R1 value should be at least 10×R2 to ensure Q1 turn-on.







Note 1: For R2 switching variations with other VIN/R1 combinations, see Typical Characteristics.


**Electrical Characteristics (  $T_A = 25^\circ\text{C}$  unless otherwise noted )**

Symbol	Parameter	Test Condition	Min	Typ	Max	Unit
<b>OFF Characteristics</b>						
$I_{FL}$	Reverse Leakage Current	$V_{IN}=8.0\text{V}$ , $V_{ON/OFF}=0\text{V}$			1	$\mu\text{A}$
$V_{SD}$	Diode Forward Voltage	$I_S=-1\text{A}$	-0.4		-1.5	V
<b>ON Characteristics</b>						
$V_{IN}$	Input Voltage Range		3.0		8.0	V
Von/Off	On/Off Voltage		1.5		8.0	V
$R_{DS(ON)}$	Static Drain-to-Source On-Resistance	$V_{ON/OFF}=1.8\text{V}$ , $V_{IN}=4.5\text{V}$ , $I_D=1.0\text{A}$		0.055	0.070	$\Omega$
		$V_{ON/OFF}=1.8\text{V}$ , $V_{IN}=2.5\text{V}$ , $I = 1.0\text{A}$		0.065	0.090	
$I_{D(on)}$	On-State (P-Channel) Drain Current	$V_{IN-OUT}\leq 0.2\text{V}$ , $V_{IN}=5\text{V}$ , $V_{ON/OFF}=1.5\text{V}$	1			A
		$V_{IN-OUT}\leq 0.3\text{V}$ , $V_{IN}=3\text{V}$ , $V_{ON/OFF}=1.8\text{V}$	1			


## Typical Operating Characteristics




**On-Resistance vs. Input Voltage**




**Thermal Transient Impedance**







**Switching Variation**



**Switching Variation**








**TECH PUBLIC**  
台舟电子

**FDC6323L-TP**

**Load Switch with Level-Shift**

[www.sot23.com.tw](http://www.sot23.com.tw)

**SOT23-6 Package Information**



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
c	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
e	0.950(BSC)		0.037(BSC)	
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°