




P/N	(L)	COLOR	额定电流
HC-TYPE B-2.0-VS15-1.5A-15	15.00mm	黑色	1.5A

Ordering Information			
HC-TYPE B - 2.0 - ** - *A - * - 15			
Type TM=Top Mount (8.1) VS=Vertical SMT (8.2,8.3) DIP=DIP (8.8)	Current Rated 1.5A 3A	Colour W=White B=Blue G=Green O=Orange P=Purple Y=Yellow	

			GENERAL TOLERANCE		制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	审核 CHECK				
			X.X	±0.30	批准 APPROVAL	产品名称 TITLE	TYPE BF 2.0 180° 立式贴片 L15.00mm	版本 REV.	A
			X.XX	±0.20	比例 SCALE	产品料号 PART NO.	HC-TYPE B-2.0-VS15-1.5A-15	单位 UNITS	mm
			X.XXX	±0.10					
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	±3.0°	投影 Projection	材料 MATERIAL			