


## **WCR250N65DV**

**Single N-Channel, 650V, 10A, Super Junction MOSFET**

<https://www.omnivision-group.com>

V <sub>DS</sub> (V)	Max. R <sub>DSON</sub> (mΩ)
650	255 @ V <sub>GS</sub> =10V



### **Description**

The WCR250N65DV is new generation of high voltage MOSFET that is utilizing an advanced charge balance mechanism for outstanding low on-resistance and lower gate charge performance. This advanced technology has been tailored to minimize conduction loss, provide superior switching performance, and withstand extreme dv/dt rate and higher avalanche energy. This device is suitable for various AC/DC power conversion in switching mode operation for higher efficiency.


### **Features**

- Extremely low gate charge
- 100% avalanche tested
- 100% R<sub>g</sub> tested


### **Applications**

- Switching applications

**DFN8X8-4L**



**Internal schematic diagram**



DV = Special Code

Y = Year

W = Week(A~z)

**Marking**

### **Order information**

Device	Package	Shipping
WCR250N65DV	DFN8X8-4L	3000/Tape&Reel

## Absolute Maximum ratings

Parameter	Symbol	Maximum	Unit
Drain-Source Voltage	V <sub>DS</sub>	650	V
Gate-Source Voltage	V <sub>GS</sub>	±30	
Continuous Drain Current	I <sub>D</sub>	10	A
		6	A
Pulsed Drain Current <sup>c</sup>	I <sub>DM</sub>	37	A
Avalanche Energy L=60mH	E <sub>AS</sub>	270	mJ
Power Dissipation <sup>b</sup>	P <sub>D</sub>	56	W
		22	
Operating Junction Temperature	T <sub>J</sub>	-55 to 150	°C
Storage Temperature Range	T <sub>STG</sub>	-55 to 150	°C

## Thermal resistance ratings







Single Operation					
Parameter	Symbol	Typical	Maximum	Unit	
Junction-to-Ambient Thermal Resistance <sup>a</sup>	t ≤ 10 s	R <sub>θJA</sub>	19	24	°C/W
	Steady State		46	55	
Junction-to-Case Thermal Resistance	Steady State	R <sub>θJC</sub>	1.8	2.3	


### Note:

- a FR-4 board (38mm X 38mm X t1.6mm, 70um Copper) partially covered with copper (645mm<sup>2</sup> area).
- b The power dissipation P<sub>D</sub> is based on T<sub>J(MAX)</sub>=150°C, using junction-to-case thermal resistance, and is more useful in setting the upper dissipation limit for cases where additional heat sinking is used.
- c Repetitive rating, ~10us pulse width, duty cycle ~1%, keep initial T<sub>J</sub> =25°C, the maximum allowed junction temperature of 150°C.
- d The static characteristics are obtained using ~380us pulses, duty cycle ~1%.


**Electronics Characteristics (Ta=25°C, unless otherwise noted)**

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
<b>OFF CHARACTERISTICS</b>						
Drain-to-Source Breakdown Voltage	BV <sub>DSS</sub>	V <sub>GS</sub> = 0 V, I <sub>D</sub> = 250uA	650			V
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	V <sub>DS</sub> = 650V, V <sub>GS</sub> = 0V			1	uA
Gate-to-source Leakage Current	I <sub>GSS</sub>	V <sub>DS</sub> = 0 V, V <sub>GS</sub> = ±30V			±100	nA
<b>ON CHARACTERISTICS</b>						
Gate Threshold Voltage	V <sub>GS(TH)</sub>	V <sub>GS</sub> = V <sub>DS</sub> , I <sub>D</sub> = 250uA	2	3	4	V
Drain-to-source On-resistance	R <sub>DS(on)</sub>	V <sub>GS</sub> = 10V, I <sub>D</sub> = 4.0A		220	255	mΩ
<b>CHARGES, CAPACITANCES AND GATE RESISTANCE</b>						
Input Capacitance	C <sub>ISS</sub>	V <sub>GS</sub> = 0 V, f = 1.0MHz, V <sub>DS</sub> = 400 V		1202		pF
Output Capacitance	C <sub>OSS</sub>			27		
Reverse Transfer Capacitance	C <sub>rss</sub>			1.8		
Total Gate Charge	Q <sub>G(TOT)</sub>	V <sub>GS</sub> = 10V, V <sub>DD</sub> = 400V, I <sub>D</sub> = 13.8A		31		nC
Gate-to-Source Charge	Q <sub>GS</sub>			7		
Gate-to-Drain Charge	Q <sub>GD</sub>			11		
Gate Resistance	R <sub>g</sub>	f=1MHz		5.8		Ω
<b>SWITCHING CHARACTERISTICS</b>						
Turn-On Delay Time	t <sub>d(ON)</sub>	V <sub>GS</sub> = 10 V, V <sub>DD</sub> = 400V, I <sub>D</sub> = 13.8A, R <sub>G</sub> =10Ω		13		ns
Rise Time	t <sub>r</sub>			10		
Turn-Off Delay Time	t <sub>d(OFF)</sub>			64		
Fall Time	t <sub>f</sub>			35		
<b>BODY DIODE CHARACTERISTICS</b>						
Forward Voltage	V <sub>SD</sub>	V <sub>GS</sub> = 0 V, I <sub>S</sub> = 4.0 A			1.5	V
Body-Diode Continuous Current	I <sub>SD</sub>				8	A
Body-Diode Pulsed Current	I <sub>SDM</sub>				37	A
Body Diode Reverse Recovery Time	T <sub>rr</sub>	IF=6.9A, V <sub>DS</sub> =400V di/dt=100A/us		310		nS
Body Diode Reverse Recovery Charge	Q <sub>rr</sub>			2.8		uC
Peak reverse recovery Current	I <sub>rrm</sub>			17.9		A


**Typical Characteristics (Ta=25°C, unless otherwise noted)**

**Output Characteristics <sup>d</sup>**

**Transfer Characteristics <sup>d</sup>**

**On-Resistance vs. Drain Current <sup>d</sup>**

 **$BV_{DS(on)}$  vs. Temperature <sup>d</sup>**

**On-Resistance vs. Junction Temperature <sup>d</sup>**

**Threshold Voltage vs. Temperature**




**Capacitance**




**Body Diode Forward Voltage <sup>d</sup>**




**Power Dissipation**





**Safe Operating Area**



**Gate Charge Characteristics**




**EOSS**




## PACKAGE OUTLINE DIMENSIONS

**DFN8X8-4L**



TOP VIEW

BOTTOM VIEW




SIDE VIEW

Symbol	Dimensions in Millimeters		
	Min.	Typ.	Max.
A	0.80	0.85	0.90
A1	0.00	0.02	0.05
A3	0.20Ref.		
b	0.90	1.00	1.10
D	7.90	8.00	8.10
E	7.90	8.00	8.10
D2	7.10	7.20	7.30
E2	4.25	4.35	4.45
e	1.90	2.00	2.10
K	2.65	2.75	2.85
L	0.40	0.50	0.60
R	0.20REF	-	-

## RECOMMENDED LAND PATTERN (Unit: mm)

DFN8X8-4L




### Notes:


*This recommended land pattern is for reference purposes only. Please consult your manufacturing group to ensure your PCB design guidelines are met.*

## TAPE AND REEL INFORMATION


**Reel Dimensions**



**Tape Dimensions**



**Quadrant Assignments For PIN1 Orientation In Tape**



RD	Reel Dimension	<input type="checkbox"/> 7inch <input checked="" type="checkbox"/> 13inch
W	Overall width of the carrier tape	<input type="checkbox"/> 8mm <input type="checkbox"/> 12mm <input checked="" type="checkbox"/> 16mm
P1	Pitch between successive cavity centers	<input type="checkbox"/> 2mm <input type="checkbox"/> 4mm <input type="checkbox"/> 8mm <input checked="" type="checkbox"/> 12mm
Pin1	Pin1 Quadrant	<input checked="" type="checkbox"/> Q1 <input type="checkbox"/> Q2 <input type="checkbox"/> Q3 <input type="checkbox"/> Q4