


650V 11A Power MOSFET

Description


XCH Semiconductor(XCH)has series Multi-EPI Super-Junction power MOSFET platforms for voltage up 500V to 1000 volts, bothwith design service and manufacturing capability, including cell,termination design and simulation.

The GSx11N65E is a Low voltage N channel Multi-EPI Super-Junction power MOSFET sample with advanced technology to have better characteristics, such as fast switchingtime. low Ciss and Crss. low on resistance and excell entavalanche characteristics.



TO-252

TO-220F



Features

RDS(ON)=0.42Ω @VGS = 10V

VDS = 650V

PKG

GSA11N65E	GSD11N65E
TO-220F	TO-252

Absolute Maximum Ratings (TC = 25° C, unless otherwise specified)

Symbol	Parameter	GSA11N65E	GSD11N65E	Unit
V _{DSS}	Drain-Source Voltage	650		V
I _D	Drain Current -Continuous (TC = 25°C) -Continuous (TC = 100°C)	11* 7*		A
I _{DM}	Drain Current - Pulsed	42		A
V _{GSS}	Gate-Source voltage	±30		V
E _{AS}	Single Pulsed Avalanche Energy	260		mJ
I _{AR}	Avalanche Current	2		A
E _{AR}	Repetitive Avalanche Energy	1		mJ
dv/dt	Peak Diode Recovery dv/dt	15		V/ns
dVds/dt	Drain Source voltage slope (Vds=480V)	50		V/ns
P _D	Power Dissipation (TC = 25°C)	31	96	W
T _J , T _{STG}	Operating and Storage Temperature Range	-55 to +150		°C
T _L	Max. Lead Temperature for Soldering Purpose, 1/8" from Case for 5 Seconds	300		°C

Thermal Characteristics


Symbol	Parameter	GSA11N65E	GSD11N65E	Unit
R _{θJC}	Thermal Resistance, Junction-to-Case	4.0	1.3	°C/W
R _{θCS}	Thermal Resistance, Case-to-Sink Typ.	--	0.5	°C/W
R _{θJA}	Thermal Resistance, Junction-to-Ambient	80	62	°C/W

■ Electrical Characteristics (T_J=25° C unless otherwise specified)


Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Off Characteristics						
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} = 0V, I _D = 250μA, T _J = 25°C	650	--	--	V
		V _{GS} = 0V, I _D = 250μA, T _J = 150°C	--	700	--	V
ΔBV _{DSS} /ΔT _J	Breakdown Voltage Temperature Coefficient	I _D = 250μA, Referenced to 25°C	--	0.6	--	V/°C
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = 650V, V _{GS} = 0V -T _J = 150°C	--	-- 10	1 -	μA μA
I _{GSSF}	Gate-Body Leakage Current, Forward	V _{GS} = 30V, V _{DS} = 0V	--	--	100	nA
I _{GSSR}	Gate-Body Leakage Current, Reverse	V _{GS} = -30V, V _{DS} = 0V	--	--	-100	nA
On Characteristics						
V _{GS(th)}	Gate Threshold Voltage	V _{DS} = V _{GS} , I _D = 250μA	2.5	--	4.5	V
R _{DS(on)}	Static Drain-Source On-Resistance	V _{GS} = 10V, I _D = 5.5A	--	0.38	0.42	Ω
g _{FS}	Forward Transconductance	V _{DS} = 40V, I _D = 5.5A	--	16	--	S
Dynamic Characteristics						
C _{iss}	Input Capacitance	V _{DS} = 25V, V _{GS} = 0V, f = 1.0MHz	--	720	-	pF
C _{oss}	Output Capacitance		--	20	-	pF
C _{rss}	Reverse Transfer Capacitance		--	1.5	--	pF
Switching Characteristics						
t _{d(on)}	Turn-On Delay Time	V _{DD} = 400V, I _D = 5.5A R _G = 20Ω (Note 4)	--	15	--	ns
t _r	Turn-On Rise Time		--	10	--	ns
t _{d(off)}	Turn-Off Delay Time		--	110	--	ns
t _f	Turn-Off Fall Time		--	9	--	ns
Q _g	Total Gate Charge	V _{DS} = 400V, I _D = 5.5A V _{GS} = 10V (Note 4)	--	32	--	nC
Q _{gs}	Gate-Source Charge		--	4	--	nC
Q _{gd}	Gate-Drain Charge		--	16	--	nC
Drain-Source Diode Characteristics and Maximum Ratings						
I _S	Maximum Continuous Drain-Source Diode Forward Current		--	--	9.2	A
I _{SM}	Maximum Pulsed Drain-Source Diode Forward Current		--	--	30	A
V _{SD}	Drain-Source Diode Forward Voltage	V _{GS} = 0V, I _S = 5.5A	--	0.9	1.5	V
t _{rr}	Reverse Recovery Time	V _{GS} = 0V, I _S = 5.5A dI _F /dt = 100A/μs	--	280	--	ns
Q _{rr}	Reverse Recovery Charge		--	3.3	--	μC

Typical Performance Characteristics


Typ. output characteristics $T_f=25\text{ }^\circ\text{C}$




Typ. output characteristics $T_f=125\text{ }^\circ\text{C}$




Typ. drain-source on-state resistance



Typ. drain-source on-state resistance




Typ. transfer characteristics




$I_D=f(V_{GS}); V_{DS}=20V$

Typ. gate charge




$V_{GS}=f(Q_{gate}), I_D=4.8A$ pulsed

Avalanche energy




$E_{AS}=f(T_j); I_D=1.8 A; V_{DD}=50 V$

Drain-source breakdown voltage




$V_{BR(DSS)}=f(T_j); I_D=1.0 mA$

Typ. capacitances



Typ. E_{oss} stored energy



Forward characteristics of reverse diode

