

MUR820 THRU MUR860

POLYIMIDE PASSIVATED SUPER FAST RECTIFIER

Reverse Voltage - 200 -600 Volts


Forward Current - 8.0Amperes

FEATURES

- Plastic package has Underwriters Laboratory Flammability Classification 94V-0
- Fast switching for high efficiency
- Low forward voltage drop
- Single rectifier construction
- High surge capability
- For use in low voltage ,high frequency inverters, free wheeling ,and polarity protection applications
- High temperature soldering guaranteed:260°C/10 seconds, 0.25"(6.35mm)from case
- Component in accordance to RoHS 2015/863/EU

MECHANICAL DATA

- Case: JEDEC TO-220AC molded plastic body
- Terminals: Lead solderable per MIL-STD-750,method 2026
- Polarity: As marked
- Mounting Position: Any
- Weight: 0.08ounce, 2.24 gram



Dimensions in inches and (millimeters)

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

(Ratings at 25°C ambient temperature unless otherwise specified ,Single phase ,half wave ,resistive or inductive load. For capacitive load,derate by 20%.)

Parameters		Symbols	MUR820	MUR840	MUR860	Units
Maximum repetitive peak reverse voltage		V_{RRM}	200	400	600	Volts
Maximum RMS voltage		V_{RMS}	140	280	420	Volts
Maximum DC blocking voltage		V_{DC}	200	400	600	Volts
Maximum average forward rectified current(see Fig.1)		$I_{(AV)}$	8.0			Amps
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC method)		I_{FSM}				Amps
Maximum instantaneous forward voltage at 8.0 A(Note 1)		V_F	0.975	1.3	1.7	Volts
Maximum instantaneous reverse current at rated DC blocking voltage(Note 1)	$T_J = 25^{\circ}C$	I_R	5			μA
	$T_J = 125^{\circ}C$		50			
Maximum Reverse Recovery Time (Note 2)		T_{rr}	35			ns
Typical thermal resistance (Note 3)		$R_{\theta C}$	2.5			$^{\circ}C/W$
Operating junction temperature range		T_J	-55 to+150			$^{\circ}C$
Storage temperature range		T_{STG}	-55 to+150			$^{\circ}C$

Notes: 1. Pulse test: 300 μ s pulse width, 1% duty cycle

2. Reverse recovery test conditions $I_F=0.5A$, $I_R=1.0A$, $I_{RR}=0.25A$

3. Thermal resistance from junction to case

FIG.1-FORWARD CURRENT DERATING CURVE




FIG.3-TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS




FIG.2-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT




FIG.4-TYPICAL REVERSE CHARACTERISTICS

