



CIRCUIT



P.C. BLAYOUT



NOTES:

1. RATING: 12VDC 20mA
2. CONTACT RESISTANCE: 100mΩ Max
3. INSULATION RESISTANCE: 100MΩ 250VDC FOR 1MIN
4. DIELECTRIC STRENGTH: 250VAC (50/60Hz) FOR 1MIN
5. LIFE TEST: 50,000 CYCLES (1Ω Max)
6. OPERATION FORCE: 250±80g
7. TRAVEL: 0.25±0.1mm

TOLERANCE			
UNLESS OTHERWISE STATED			
X.X	±0.25	∠	±2°
X.XX	±0.15	UNIT	mm
REV	A/04	SCALE	1:1
SIZE	A4	SHEET	1 OF 1

7	COVER	ABS
6	LED	GaAsP/GaP
5	TERMINAL	H65(C2680)
4	CONTACT	SUS
3	BUTTON	PA66
2	FIXITY	PA66
1	HOUSING	PA66
ITEM	PARTNAME	MATERIAL



版本 VERSION		A1		比例尺 SCALE		1:1		日期 DATE		2022.09.07		品名 TITLE		图号 DRAWING NO	
A 1	修正图纸未显示定位孔的圆圈的错误等	2022.09.07		核准		核对		绘图	孙成	DS01-105RFL-U		XXXXXXX			
版本 VER	变更说明 CHANGE DESCRIPTION	日期 DATE	ECN NO.	APPROVED BY		CHECKED BY		DRAWN BY							