



SHENZHEN HAOLIN ELECTRONICS TECHNOLOGY CO., LTD

SOT-23 Encapsulate Three-terminal Voltage Regulators

78L12

Three-terminal positive voltage regulator

FEATURES

Maximum output current

 I_{OM} : 0.1A

Output voltage

 V_o : 12 V

Continuous total dissipation

 P_D : 0.625W

SOT-23



1. OUT

2. IN

3. GND


ABSOLUTE MAXIMUM RATINGS (Operating temperature range applies unless otherwise specified)

Parameter	Symbol	Value	Unit
Input Voltage	V_I	35	V
Operating Junction Temperature Range	T_{OPR}	0~+150	°C
Storage Temperature Range	T_{STG}	-55~+150	°C

ELECTRICAL CHARACTERISTICS AT SPECIFIED VIRTUAL JUNCTION TEMPERATURE ($V_I=19V$, $I_O=40mA$, $C_J=0.33\mu F$, $C_O=0.1\mu F$, unless otherwise specified)

Parameter	Symbol	Test conditions	Min	Typ	Max	Unit
Output voltage	V_o	25°C	11.5	12	12.5	V
		14V≤ V_I ≤27V, $I_O=1mA-40mA$	11.4	12	12.6	V
		$I_O=1mA-70mA$	0-125°C	11.4	12	V
Load Regulation	ΔV_o	$I_O=1mA-100mA$	25°C	22	100	mV
		$I_O=1mA-40mA$	25°C	13	50	mV
Line regulation	ΔV_o	14.5V≤ V_I ≤27V	25°C	55	250	mV
		16V≤ V_I ≤27V	25°C	49	200	mV
Quiescent Current	I_Q		25°C	4.3	6.5	mA
Quiescent Current Change	ΔI_Q	16V≤ V_I ≤27V	0-125°C		1.5	mA
		1mA≤ I_O ≤40mA	0-125°C		0.1	mA
Output Noise Voltage	V_N	10Hz≤f≤100KHz	25°C	70		uV
Ripple Rejection	RR	15V≤ V_I ≤25V, f=120Hz	0-125°C	37	42	dB
Dropout Voltage	V_d		25°C	1.7		V

TYPICAL APPLICATION



Note : Bypass capacitors are recommended for optimum stability and transient response and should be located as close as possible to the regulators.