


10	7382	Specification	Super Small SMD Tactile Switches SOG-152HNT	承認/Approved	検閲/Checked	図面/Drawn
				SW検閲部 '11.06.10 寺下	SW検閲部 '11.06.10 川口	SW検閲部 '11.06.10 菊池
Customer's Name		Customer's Parts No.		General Specification		
				S66-1570		
				Issued '11.06.10		


Confidential

- 1) The items stipulated in this specification are prior to the "General Specification".
- 2) When not stipulated in this specification the items "General Specification" are applied.



Operating force	1.6±0.5 [N]
Return force	0.2 [N] Min
Travel	0.15±0.1 [mm]
Contact Resistance	1.0 [Ω] Max

Circuit Diagram



メタルマスク厚: 100μm
Metal Mask thickness: 100μm

環境区分	G
該非判定結果	N
開発区分	2
Development Class	
公差	±0.15
Tolerance	
組立図	66-K056A
Assembly Drwn No.	

Revision				第三角法	尺度	Development	組立図
				Third Angle	Scale	Tolerance	Assembly Drwn No.
				Projection	10.000	±0.15	66-K056A
品質保証工程図	検査標準図	機種コード	部品コード	部品コード	部品コード	部品コード	部品コード
Product Manual	Inspect. Manual	Model Code	Code	Ident. No.	File No.		
Q66-0788	166-8522	1116	R 66		7382		01