

# MMTL432

## SOT-23 Encapsulate Adjustable Reference Source


Adjustable Accurate Reference Source

### DEVICE DESCRIPTION

The TL432 is a three-terminal Shunt Voltage Reference providing a highly accurate 1.24V. The CJ432 thermal stability and wide operating current, makes it suitable for all variety of applications that are looking for a low cost solution with high performance.

### FEATURES

- Low dynamic output impedance
- The effective temperature compensation in the working range of full temperature
- Low output noise voltage
- Fast on-state response
- Sink current capability of 0.1mA to 100mA



### APPLICATION

- Shunt Regulator
- High-Current Shunt Regulator
- Precision Current Limiter

### ABSOLUTE MAXIMUM RATINGS (Operating temperature range applies unless otherwise specified)




| Parameter                                   | Symbol          | Value    | Units         |
|---|-----------------|----------|---------------|
| Cathode Voltage                             | $V_{KA}$        | 18       | V             |
| Cathode Current Range (continuous)          | $I_{KA}$        | 100      | mA            |
| Reference Input Current Range               | $I_{ref}$       | 6        | $\mu A$       |
| Power Dissipation                           | $P_D$           | 350      | mW            |
| Thermal Resistance from Junction to Ambient | $R_{\theta JA}$ | 357      | $^{\circ}C/W$ |
| Operating Temperature                       | $T_{opr}$       | 0~+70    | $^{\circ}C$   |
| Junction Temperature                        | $T_J$           | 150      | $^{\circ}C$   |
| Storage Temperature                         | $T_{stg}$       | -65~+150 | $^{\circ}C$   |

**ELECTRICAL CHARACTERISTICS ( $T_a=25^\circ\text{C}$  unless otherwise specified)**


| Parameter   | Symbol                                | Test conditions   | Min    | Typ | Max    | Unit          |
|---|---------------------------------------|---|--------|-----|--------|---------------|
| Reference input voltage (Fig 1)   | $V_{\text{ref}}$                      | $V_{KA}=V_{\text{REF}}, I_{KA}=10\text{mA}$   | 1.2214 |     | 1.2586 | V             |
| Deviation of reference voltage over full temperature range (Fig 1)                  | $\Delta V_{\text{ref(DEV)}}$          | $V_{KA}=V_{\text{REF}}, I_{KA}=10\text{mA}$<br>$0^\circ\text{C} \leq T_a \leq 70^\circ\text{C}$             |        |     | 16     | mV            |
| Ratio of change in reference input voltage to the change in cathode voltage (Fig 2) | $\Delta V_{\text{ref}}/\Delta V_{KA}$ | $I_{KA}=10\text{mA},$<br>$\Delta V_{KA}=1.25\text{V}\sim15\text{V}$   |        |     | 2.4    | mV/V          |
| Deviation of reference input current over full temperature range (Fig 2)            | $\Delta I_{\text{ref}}/\Delta T$      | $I_{KA}=10\text{mA}, R_1=10\text{k}\Omega,$<br>$R_2=\infty, 0^\circ\text{C} \leq T_a \leq 70^\circ\text{C}$ |        |     | 0.6    | $\mu\text{A}$ |
| Minimum cathode current for regulation (Fig 1)                                      | $I_{KA(\min)}$                        | $V_{KA}=V_{\text{REF}}$   |        |     | 0.1    | mA            |
| Off-state cathode current(Fig 3)  | $I_{\text{off}}$                      | $V_{KA}=15\text{V}, V_{\text{REF}}=0$   |        |     | 0.5    | $\mu\text{A}$ |
| Dynamic impedance   | $Z_{KA}$                              | $V_{KA}=V_{\text{REF}}, I_{KA}=0.1\sim20\text{mA},$<br>$f \leq 1.0\text{kHz}$                               |        |     | 0.5    | $\Omega$      |

**CLASSIFICATION OF  $V_{\text{ref}}$** 



|       |               |               |
|-------|---------------|---------------|
| Rank  | 1%            | 1.5%          |
| Range | 1.2276~1.2524 | 1.2214~1.2586 |



Test Circuit for  $V_{KA}=V_{ref}$





**Change in Reference Input Voltage versus Cathode Voltage**





Test Circuit for  $V_{KA} = V_{ref}(1+R_1/R_2)+R_1 \cdot I_{ref}$

**Reference Input Current versus Ambient Temperature**



Test Circuit for  $I_{ref}$

**Off-State Cathode Current versus Ambient Temperature**




Test Circuit for  $I_{off}$

### PACKAGE OUTLINE

Plastic surface mounted package; 3 leads

SOT-23



| Symbol | Dimension in Millimeters |       |
|--------|--------------------------|-------|
|        | Min                      | Max   |
| A      | 0.95                     | 1.40  |
| B      | 1.78                     | 2.04  |
| bp     | 0.35                     | 0.50  |
| C      | 0.08                     | 0.19  |
| D      | 2.70                     | 3.10  |
| E      | 1.20                     | 1.65  |
| HE     | 2.20                     | 3.00  |
| A1     | 0.100                    | 0.013 |
| Lp     | 0.20                     | 0.50  |