



General Description

- 100% UIS Tested
- Advanced Trench Technology
- Low Gate Charge
- High Current Capability
- RoHS and Halogen-Free Compliant


Product Summary

V _{DS}	40	V
R _{DSON,TYP}	2.2	mΩ
I _D	170	A

Applications

- SMPS Synchronous Rectification
- DC/DC Converters
- Or-ing

TO-263 Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V _{DS}	Drain-Source Voltage	40	V
V _{GS}	Gate-Source Voltage	±20	V
I _D @T _C =25°C	Continuous Drain Current, V _{GS} @ 10V ^{1,6}	170	A
I _D @T _C =100°C	Continuous Drain Current, V _{GS} @ 10V ^{1,6}	142	A
I _{DM}	Pulsed Drain Current ²	400	A
EAS	Single Pulse Avalanche Energy ³	462	mJ
I _{AS}	Avalanche Current	43	A
P _D @T _C =25°C	Total Power Dissipation ⁴	178	W
T _{STG}	Storage Temperature Range	-55 to 150	°C
T _J	Operating Junction Temperature Range	-55 to 150	°C

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
R _{θJA}	Thermal Resistance Junction-Ambient ¹	---	50	°C/W
R _{θJC}	Thermal Resistance Junction-Case ¹	---	0.7	°C/W



Electrical Characteristics ($T_J=25^\circ\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{\text{GS}}=0\text{V}$, $I_D=250\mu\text{A}$	40	---	---	V
$R_{\text{DS}(\text{ON})}$	Static Drain-Source On-Resistance ²	$V_{\text{GS}}=10\text{V}$, $I_D=20\text{A}$	---	2.2	2.6	$\text{m}\Omega$
		$V_{\text{GS}}=4.5\text{V}$, $I_D=20\text{A}$	---	2.8	3.6	
$V_{\text{GS}(\text{th})}$	Gate Threshold Voltage	$V_{\text{GS}}=V_{\text{DS}}$, $I_D=250\mu\text{A}$	1.2	1.6	2.2	V
I_{DSS}	Drain-Source Leakage Current	$V_{\text{DS}}=32\text{V}$, $V_{\text{GS}}=0\text{V}$, $T_J=25^\circ\text{C}$	---	---	1	uA
		$V_{\text{DS}}=32\text{V}$, $V_{\text{GS}}=0\text{V}$, $T_J=55^\circ\text{C}$	---	---	5	
I_{GSS}	Gate-Source Leakage Current	$V_{\text{GS}}=\pm 20\text{V}$, $V_{\text{DS}}=0\text{V}$	---	---	± 100	nA
g_{fs}	Forward Transconductance	$V_{\text{DS}}=5\text{V}$, $I_D=20\text{A}$	---	53	---	S
R_g	Gate Resistance	$V_{\text{DS}}=0\text{V}$, $V_{\text{GS}}=0\text{V}$, $f=1\text{MHz}$	---	1.9	---	Ω
Q_g	Total Gate Charge	$V_{\text{DS}}=15\text{V}$, $V_{\text{GS}}=10\text{V}$, $I_D=20\text{A}$	---	68	---	nC
Q_{gs}	Gate-Source Charge		---	10.3	---	
Q_{gd}	Gate-Drain Charge		---	14.5	---	
$T_{\text{d}(\text{on})}$	Turn-On Delay Time	$V_{\text{DD}}=15\text{V}$, $V_{\text{GS}}=10\text{V}$, $R_{\text{G}}=3.3\Omega$, $I_D=20\text{A}$	---	11.5	---	ns
T_r	Rise Time		---	40.3	---	
$T_{\text{d}(\text{off})}$	Turn-Off Delay Time		---	44.5	---	
T_f	Fall Time		---	26.4	---	
C_{iss}	Input Capacitance	$V_{\text{DS}}=20\text{V}$, $V_{\text{GS}}=0\text{V}$, $f=1\text{MHz}$	---	3872	---	pF
C_{oss}	Output Capacitance		---	1219	---	
C_{rss}	Reverse Transfer Capacitance		---	112	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_s	Continuous Source Current ^{1,6}	$V_G=V_D=0\text{V}$, Force Current	---	---	130	A
V_{SD}	Diode Forward Voltage ²	$V_{\text{GS}}=0\text{V}$, $I_s=1\text{A}$, $T_J=25^\circ\text{C}$	---	---	1.2	V

Note :

- 1.The data tested by surface mounted on a 1 inch² FR-4 board with 2OZ copper.
- 2.The data tested by pulsed , pulse width $\leq 300\text{us}$, duty cycle $\leq 2\%$
- 3.The EAS data shows Max. rating . The test condition is $V_{\text{DD}}=25\text{V}$, $V_{\text{GS}}=10\text{V}$, $L=0.5\text{mH}$, $I_{\text{AS}}=43\text{A}$
- 4.The power dissipation is limited by 150°C junction temperature
- 5.The data is theoretically the same as I_D and I_{DM} , in real applications , should be limited by total power dissipation.
- 6.Package limitation current is 210A.



Typical Characteristics




Fig.1 Typical Output Characteristics




Fig.3 Source Drain Forward Characteristics




Fig.5 Normalized $V_{GS(th)}$ vs T_J




Fig.2 On-Resistance vs G-S Voltage




Fig.4 Gate-Charge Characteristics




Fig.6 Normalized $R_{DS(on)}$ vs T_J



HUASHUO
SEMICONDUCTOR

HSH4070

N-Ch 40V Fast Switching MOSFETs




Fig.7 Capacitance




Fig.8 Safe Operating Area




Fig.9 Normalized Maximum Transient Thermal Impedance




Fig.10 Switching Time Waveform





Fig.11 Unclamped Inductive Switching



SYMBOLS	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	4.370	4.770	0.172	0.188
A1	1.220	1.420	0.048	0.056
A2	2.200	2.890	0.087	0.114
A3	0.000	0.250	0.000	0.010
b	0.700	0.960	0.028	0.038
b1	1.170	1.470	0.046	0.058
c	0.300	0.530	0.012	0.021
D1	8.500	9.300	0.335	0.366
D4	6.600	-	0.260	-
E	9.860	10.36	0.388	0.408
E5	7.060	-	0.278	-
e	2.540 BSC		0.100 BSC	
H	14.70	15.70	0.579	0.618
H2	1.070	1.470	0.042	0.058
L	2.000	2.600	0.079	0.102
L1	1.400	1.750	0.055	0.069
L4	0.250 BSC		0.010 BSC	
Θ	0°	9°	0°	9°