

62P	55.42	63.50	69.32	2.41	0.58
44P	38.96	47.04	53.04	2.29	0.51
26P	25.25	33.32	39.14	2.29	0.51
15P	16.92	24.99	30.81	2.29	0.25
POS NO.	DIMENSION				

SPECIFICATIONS:
 Current rating:3.0A AC/DC
 Voltage rating:250V AC/DC
 Contact resistance:30m ohm MAX
 Insulation resistance:5000M ohm MIN
 Withstanding voltage:1000V AC for one minute
 Operating temperature range:-40°C ~ +85°C

MATERIAL AND FINISH
 Insulator:PBT+30%G.F(UL94V-0)
 Contact:Copper Alloy Nickel Undercoated
 Selective Gold Plated
 SHELL: Metal Iron With Tin Plated

PART NO.
 Z-SUBHR * M * * 2 * * * *

NO. OF CONTACTS
 B=15PIN
 D=26PIN
 F=44PIN
 G=62PIN
 H=78PIN

TYPE
 M=MALE

MOUNTING OPTIONS
 6=SCREWED HEX SCREW ON BOARD LOCK
 7=RIVETED W/ BOARD LOCK/WASHER
 8=RIVETED W/BOARD LOCK/WASHER/HEX SCREW
 9=RIVETED W/ BOARD LOCK/WASHER/ ATTACHED HEX SCREW
 C=SCERWED HEX SCREW DIRECT RIVETING NUT LOCK


LOGO
 0=NO LOGO
 2=NEXTRON LOGO



INSULATOR COLOR
 0=BLACK
 6=BLUE
 9=WHITE


INSULATOR MATERIAL
 0=PBT
 2=NYLON

PLATED
 A=GOLD 1u"/LIGHT TIN
 B=GOLD 3u"/LIGHT TIN
 C=GOLD 5u"/LIGHT TIN
 E=GOLD 15u"/LIGHT TIN
 F=GOLD 30u"/LIGHT TIN

CONTACT MATERIAL
 2=BRASS

NUT POST HEIGHT(H*L) 
 0=5.8*12.8
 1=4.8*11.8



B	ECN-19105  B=1	2019/11/14
A	ADD LOGO MARK	2016/06/11
REV.	DESCRIPTION	DATE

UNITS: ■ mm □ inch	SIZE A3	NAME: D-SUB HR TYPE MALE	 NEXTRONICS ENGINEERING CORP.								
	GENERAL TOLERANCE: (UNLESS SPECIFIED)					PART NO: Z-SUBHRXMXX2XXXX	TITLE: CUSTOMER DWG				
4 PLACE	± **	± **	APPD: Linson 曾偉雄	2019/12/02	DWG NO: 010-0000-F38						
3 PLACE	± **	± **	CHKD: Linson 曾偉雄	2019/12/02							
2 PLACE	± 0.20	± **	DRAW:		<table border="1"> <tr> <td>SCALE</td> <td>SHEET</td> <td>REV.</td> </tr> <tr> <td>1/1</td> <td>1/1</td> <td>B</td> </tr> </table>	SCALE	SHEET	REV.	1/1	1/1	B
SCALE	SHEET	REV.									
1/1	1/1	B									
1 PLACE	± 0.30	± **	DESIGN: Lu 陳惠枝	2019/11/29							
ANGLES	X° ± 3°										

