



UG8KB05 THRU UG8KB100


BRIDGE RECTIFIERS

Features

- Glass passivated die construction
- High surge current capability
- High surge current capability
- designed for surface mount application
- Plastic material-UL flammability 94V-0

Mechanical Data

- Case: D3K, molded plastic
- Terminal: Plated leads solderable per MIL-STD 202, Method 208
- Polarity: As Marked on case
- Mounting Position: Any
- Marking: Type Number
- Lead Free: For RoHS/Lead Free Version



Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified.
Single Phase, half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%.

TYPE NUMBER (NOTE2)	SYMBOL	UG8K B05	UG8K B10	UG8K B20	UG8K B40	UG8K B60	UG8K B80	UG8K B100	UNIT
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V _{RRM}	50	100	200	400	600	800	1000	V
	V _{RWM}								
	V _{DC}								
RMS Reverse Voltage	V _{RMS}	35	70	140	280	420	560	700	V
Average Rectified Output Current Without heat sink @T _c =90℃ With heat sink @T _c =90℃	IF(AV)	4.0 8.0							A
Non-Repetitive Peak Forward Surge Current 8.3ms Single half sine-wave superimposed on rated load (JEDEC Method)	I _{FSM}	150							A
I ² t Rating for Fusing (t < 8.3ms)	I ² t	93.375							A ² s
Forward Voltage per element @IF=8.0A	V _{FM}	1.1							V
Maximum DC reverse current at T _A =25℃ rated DC blocking voltage per leg T _A =125℃	I _R	5.0 500							uA
Typical Junction Capacitance per leg	C _J	21							pF
Typical thermal resistance per leg(Note 1)	R _{θJA}	55							℃/W
	R _{θJL}	15							
Operating and Storage Temperature Range	T _J , T _{STG}	-55 to +150							℃

Note:1. Measured at 1.0 MHZ and applied reverse voltage of 4.0VD.C.



UG8KB05 THRU UG8KB100 BRIDGE RECTIFIERS

Characteristic Curves ($T_A=25^\circ\text{C}$ unless otherwise noted)

Fig. 1 Output Current Derating Curve




Fig. 2 Typical Forward Characteristics (per leg)




Fig. 3 Maximum Peak Forward Surge Current (per leg)




Fig. 4 Typical Junction Capacitance Per Diode




Fig. 5 Typical Reverse Characteristics (per element)

