

F

E

D

C

B

A

F

E




D

C

B

A

REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	INITIAL RELEASE.	2013.01.24	李芳忠



Specifications
Current Rating:3Amp
Insulation Resistance:1000MΩMin.
Dielectric Withstanding Voltage:600VAC
Contact Resistance:20mΩMax.
Operating Temperature:-40°C to +105°C
Materials
Contact Material: Brass
Insulator Material:High Temperature Thermoplastic, UL 94V-0 LCP or the equivalent material
All materials must meet Greenconn requirement for environment protection.

Ordering Information

G PHB218 - XX XX A 004 C 1 B X


No. of Pins per Row
03~30

Standard Plating
02=Gold Flash
Selective Plating
01=Tin
05=Gold Flash/Tin

Color
1=Black

Standard Packing
A=box
Selective Packing
C=Tube

Recommended P.C.Board Layout
(Tolerance:±0.05)



格菱股份有限公司
Greenconn Corporation

GENERAL TOLERANCE		DESIGN: 李芳忠	DATE: 2013.01.24	DWG. NO.	TITLE. 2.54 PIN HEADER DUAL ROWS R/A TYPE CONNECTOR
X.*±5.0°	X.±0.30	CHECKED: 劉北平	DATE: 2013.01.24	GPHB218-CA4CB	
.X*±3.0°	.X±0.25	AUDITED: 李輝	DATE: 2013.01.24	PART NO.	
.XX*±2.0°	.XX±0.15	APPROVED: cc_Li	DATE: 2013.01.24	GPHB218-XXXX A004C1BX	
.XXX*±1.0°	.XXX±0.10				

REV.	UNIT.	SCALE.	PAGE.	
01	mm	3:1	1/1	