





REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
A00	NEW	INTERIM INITIAL RELEASE.	2021.12.06	郭康

Specifications
Current Rating:2.0Amp
Insulation Resistance:1000MΩMin.
Dielectric Withstanding Voltage:500VAC
Contact Resistance:20mΩMax.
Operating Temperature:−40°C to +105°C
Materials
Contact Material:Copper alloy
High Temperture Thermoplastic: Suitable for Reflow Soldering Process UL 94V−0 (LCP, Nylon HTN,) Regular Thermoplastic: Only Suitable for Wave Soldering Process (PBT).
All materials must meet Greenconn hazardous substances control standards.

Recommended P.C.Board Layout
(Tolerance:±0.05)



Ordering Information

G PFA402 − XX XX A 018 X X X X

No. of Pins per Row
02~40

Standard Plating
02=Gold Flash
Selective Plating
01=Tin
05=Gold Flash/Tin

Insulator Material
A=PBT (Halogen)
K=PBT (Halogen Free)
R=NYLON−HTN
C=LCP


Color
1=Black
5=Natural

Contact Material
A=Phosphor Bronze
B=Brass

Standard Packing
A=box
Selective Packing
C=Tube(A00)
D=Tape&Reel



3RD.ANG
PROJ.



PAGE.
1/1

GENERAL TOLERANCE

X'±3.0'	X±0.25
.X'±2.0'	.X±0.20
.XX'±1.0'	.XX±0.13
.XXX'±0.5'	.XXX±0.08

DESIGNED: 郭康

DATE:2021.12.06

CHECKED:

DATE:

APPROVED:

DATE:

DWG. NO.

GPFA402−CA018

PART NO.

GPFA402−XXXX A018XXXX

TITLE.

2.00 PIN
HEADER FOUR
ROWS DIP TYPE

REV.
A00

UNIT.
mm

SCALE.
4:1