

### ● General Description

The AGM502 combines advanced trench MOSFET technology with a low resistance package to provide extremely low  $R_{DS(ON)}$ .

This device is ideal for load switch and battery protection applications.

### ● Features

- Advance high cell density Trench technology
- Low  $R_{DS(ON)}$  to minimize conductive loss
- Low Gate Charge for fast switching
- Low Thermal resistance



### ● Application

- MB/VGA Vcore
- SMPS 2<sup>nd</sup> Synchronous Rectifier
- POL application
- BLDC Motor driver

### Product Summary

BVDSS	RDSON	ID
60V	1.2mΩ	0.8A

### SOT-523 Pin Configuration



### Package Marking and Ordering Information

Device Marking	Device	Device Package	Reel Size	Tape width	Quantity
50A	AGM502	SOT-523	----	----	3000

**Table 1. Absolute Maximum Ratings (TA=25°C)**

Symbol	Parameter	Value	Unit
VDS	Drain-Source Voltage (VGS=0V)	60	V
VGS	Gate-Source Voltage (VDS=0V)	±20	V
ID	Drain Current-Continuous(TA=25°C) <b>(Note 1)</b>	0.8	A
	Drain Current-Continuous(TA=100°C)	--	A
IDM (pluse)	Drain Current-Continuous@ Current-Pulsed <b>(Note 2)</b>	1.6	A
PD	Maximum Power Dissipation(TA=25°C)	0.43	w
	Maximum Power Dissipation(TA=100°C)	0.17	w
EAS	Avalanche energy <b>(Note 3)</b>	--	mJ
TJ,TSTG	Operating Junction and Storage Temperature Range	-55 To 150	°C

**Table 2. Thermal Characteristic**

Symbol	Parameter	Typ	Max	Unit
RθJA	Thermal Resistance Junction-ambient (Steady State) <sup>1</sup>	---	290	°C/W
RθJC	Thermal Resistance Junction-Case <sup>1</sup>	---	--	°C/W

**Table 3. Electrical Characteristics (TA=25°C unless otherwise noted)**





Symbol	Parameter	Conditions	Min	Typ	Max	Unit
<b>On/Off States</b>						
BVDSS	Drain-Source Breakdown Voltage	VGS=0V ID=250μA	60	--	--	V
IDSS	Zero Gate Voltage Drain Current	VDS=60V, VGS=0V	--	--	1	μA
IGSS	Gate-Body Leakage Current	VGS=±20V, VDS=0V	--	--	±100	nA
VGS(th)	Gate Threshold Voltage	VDS=VGS, ID=250μA	0.5	--	1.2	V
gFS	Forward Transconductance	VDS=5V, ID=0.2A	--	--	--	S
RDS(on)	Drain-Source On-State Resistance	VGS=10V, ID=0.2A	--	1.2	1.5	mΩ
		VGS=4.5V, ID=0.1A	--	1.3	1.8	mΩ
<b>Dynamic Characteristics</b>						
Ciss	Input Capacitance	VDS=25V, VGS=0V, F=1MHZ	--	34	--	pF
Coss	Output Capacitance		--	3.6	--	pF
Crss	Reverse Transfer Capacitance		--	2.3	--	pF
Rg	Gate resistance	VGS=0V, VDS=0V, f=1.0MHz	--	--	--	Ω
<b>Switching Times</b>						
td(on)	Turn-on Delay Time	VGS=10V, VDS=30V, RGEN=4.5Ω, ID=0.2A	--	2.7	--	nS
tr	Turn-on Rise Time		--	2.7	--	nS
td(off)	Turn-Off Delay Time		--	9.9	--	nS
tf	Turn-Off Fall Time		--	10.8	--	nS
Qg	Total Gate Charge	VGS=10V, VDS=30V, ID=0.2A	--	1.4	--	nC
Qgs	Gate-Source Charge		--	0.4	--	nC
Qgd	Gate-Drain Charge		--	0.2	--	nC
<b>Source-Drain Diode Characteristics</b>						
ISD	Source-Drain Current(Body Diode)		--	--	0.8	A
VSD	Forward on Voltage	VGS=0V, IS=0.2A	--	--	1.0	V
trr	Reverse Recovery Time	IF=0.2A , dI/dt=100A/μs ,	--	--	--	ns
Qrr	Reverse Recovery Charge	TJ=25°C	--	--	--	nc

Notes 1.The maximum current rating is package limited.





Notes 2.Repetitive Rating: Pulse width limited by maximum junction temperature

Notes 3.EAS condition: TJ=25°C





## Typical Characteristics



## Typical Characteristics (cont.)




## Typical Characteristics (cont.)




# Package Dimensions

## SOT523 Package



Typical Soldering Pattern:



DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	0.70	0.90	0.028	0.035
A1	0.00	0.10	0.000	0.004
A2	0.70	0.80	0.028	0.031
b1	0.15	0.25	0.006	0.010
b2	0.25	0.35	0.010	0.014
c	0.10	0.20	0.004	0.008
D	1.50	1.70	0.059	0.067
E	0.70	0.90	0.028	0.035
E1	1.45	1.75	0.057	0.069
e	0.50 TYP.		0.020 TYP.	
e1	0.90	1.10	0.035	0.043
L	0.40 REF.		0.016 REF.	
L1	0.10	0.30	0.004	0.012
$\theta$	0°	8°	0°	8°


Disclaimer:

The information provided in this document is believed to be accurate and reliable. however, Shenzhen Core Control Electronics Technology Co., Ltd. does not assume any responsibility for the following consequences Do not consider the use of such information or use beyond its scope.

The information mentioned in this document may be changed at any time without notice.

The products and information provided in this document do not infringe patents. Shenzhen Core Control Electronics Technology Co., Ltd. assumes no responsibility for any infringement of any other rights of third parties. The result of using such products and information.

This document is the second version issued on October 10, 2022. This document replaces and Replace all previously provided information.

 It is a registered trademark of Shenzhen Core Control Electronics Technology Co., Ltd.

Copyright © 2017 Shenzhen Core Control Electronics Technology Co., Ltd. all rights reserved.