













NOTE1. THE RECOMMENDED TAPPING SCREW IS SPECIFIED IN JIS B 1122 2ND GRADE 3×6 AND B-TIGHT SCREW 3×6.
NOTE2. MATERIAL CODE APPEARS IN RAISED LETTERS.
NOTE3. MOLDING LOT (YEAR AND MONTH) APPEARS IN RAISED LETTERS.
NOTE4. COMPANY LOGO "JAE" & CAVITY NUMBER APPEARS IN RAISED LETTERS.
NOTE5. THE ASSEMBLY LOT NO. IS INDICATED.
NOTE6. TERMINAL NUMBER APPEARS IN RAISED LETTERS.

注1. 推奨タッピンねじは、JIS B 1122 2種 3×6及びBタイトねじ 3×6。
注2. 材料名を浮き出す。
注3. ハウジングの成形ロット(年月)を浮き出す。
注4. 社標、キャビティ番号を浮き出す。
注5. 組立ロット番号を表記する。
注6. 端子番号を浮き出す。

REFERENCE ONLY
JAE

5	060 SHORT TERMINAL-2	2	COPPER ALLOY	TIN PLATING	—
4	060 SHORT TERMINAL-1	2	COPPER ALLOY	TIN PLATING	—
3	025 SHORT TERMINAL-2	10	BRASS	TIN PLATING	—
2	025 SHORT TERMINAL-1	10	BRASS	TIN PLATING	—
1	HOUSING	1	SPS-GF30	—	COLOR: GRAY

符号 NO.	名 称 DESCRIPTION	個 数 QTY.	材 料 MATERIAL	仕 上 FINISH	備 考 REMARKS
仕様書 (SPECIFICATION)					
JACS-10940 JAHL-10940		第1版 (ORIGINAL DATE) 19/JUN/2013		尺度 (SCALE) 2:1	シリーズ (SERIES) MX58
一般公差 (GENERAL TOLERANCE)		製図 DR.	—	名称 (TITLE) MX58024NFB (MALE CONNECTOR)	
寸法 (DIMENSION)		担当 CHK.	T. KINOSHITA		
角度 (ANGLES)		査閲 APPD.	Y. WATANABE		
× ±0.8		承認 APPD.	A. OONO	質量 (MASS) 8.7g	図面番号 (DRAWING NO.) SJ112382
× ±0.4		単位 (UNIT): mm		JAE	
× ±0.1				JAPAN AVIATION ELECTRONICS INDUSTRY, LTD.	
× × ±				図面番号 (DRAWING NO.) SJ112382	