



LBC856BDW1T1G

S-LBC856BDW1T1G

Dual General Purpose Transistors

1. FEATURES

- We declare that the material of product compliance with RoHS requirements and Halogen Free.
- S- prefix for automotive and other applications requiring unique site and control change requirements; AEC-Q101 qualified and PPAP capable.



2. DEVICE MARKING AND ORDERING INFORMATION

Device	Marking	Shipping
LBC856BDW1T1G	3B	3000/Tape&Reel
LBC856BDW1T3G	3B	10000/Tape&Reel

3. MAXIMUM RATINGS(Ta = 25°C)

Parameter	Symbol	Limits	Unit
Collector–Emitter Voltage	VCEO	-65	V
Collector–Base Voltage	VCBO	-80	V
Emitter–Base Voltage	VEBO	-5	V
Collector Current(Continuous)	IC	-100	mA

4. THERMAL CHARACTERISTICS





Parameter	Symbol	Limits	Unit
Total Device Dissipation	PD	250	mW
FR– 4 Board (Note 1)			
Derate above 25°C		2.0	mW/°C
Thermal Resistance, Junction to Ambient	RθJA	500	°C/W
Junction and Storage Temperature	TJ, Tstg	-55 ~ +150	°C

1.30.0mm×25.0mm×1.6mm(FR4)




5. ELECTRICAL CHARACTERISTICS (Ta= 25°C)

Characteristic	Symbol	Min.	Typ.	Max.	Unit
OFF CHARACTERISTICS					
Collector–Emitter Breakdown Voltage (IC = -10 mA)	V(BR)CEO	-65	-	-	V
Collector–Emitter Breakdown Voltage (IC = -10 μA, VEB = 0)	V(BR)CES	-80	-	-	V
Collector–Base Breakdown Voltage (IC = -10 μA)	V(BR)CBO	-80	-	-	V
Emitter–Base Breakdown Voltage (IE = -1.0 μA)	V(BR)EBO	-5	-	-	V
Collector Cutoff Current (VCB = -30 V) (VCB = -30 V, TA = 150°C)	ICBO	-	-	-15 -4	nA μA
ON CHARACTERISTICS					
DC Current Gain (IC = -10 μA, VCE = -5.0 V) (IC = -2.0 mA, VCE = -5.0 V)	hFE	- 220	320 290	- 475	
Collector–Emitter Saturation Voltage (IC = -10 mA, IB = -0.5 mA) (IC = -100 mA, IB = -5.0 mA)	VCE(sat)	- -	- -	-0.3 -0.65	V
Base–Emitter Saturation Voltage (IC = -10 mA, IB = -0.5 mA) (IC = -100 mA, IB = -5.0 mA)	VBE(sat)	- -	-0.7 -0.9	- -	V
Base–Emitter Voltage (IC = -2.0 mA, VCE = -5.0 V) (IC = -10 mA, VCE = -5.0 V)	VBE(on)	-0.6 -	- -	-0.75 -0.82	V
SMALL–SIGNAL CHARACTERISTICS					
Current–Gain — Bandwidth Product (IC = -10 mA, VCE = -5.0 V, f = 100 MHz)	fT	100	-	-	MHz
Output Capacitance (VCB = -10 V, f = 1.0 MHz)	Cobo	-	-	4.5	pF
Noise Figure(IC = -0.2 mA, VCE = -5.0 V, RS = 2.0 kΩ, f = 1.0 KHz, BW = 200 Hz)	NF	-	-	10	dB

6.ELECTRICAL CHARACTERISTICS CURVES




6.ELECTRICAL CHARACTERISTICS CURVES(Con.)



7.OUTLINE AND DIMENSIONS


Notes:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH. MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF BASE MATERIAL.
4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS.



DIM	MILLIMETERS			INCHES		
	MIN	NOM	MAX	MIN	NOM	MAX
A	---	---	1.10	---	---	0.043
A1	0.00	---	0.10	0	---	0.004
A2	0.70	0.90	1.00	0.027	0.035	0.039
b	0.15	0.20	0.25	0.006	0.008	0.01
C	0.08	0.15	0.22	0.003	0.006	0.009
D	1.80	2.00	2.20	0.07	0.078	0.086
E	2.00	2.10	2.20	0.078	0.082	0.086
E1	1.15	1.25	1.35	0.045	0.049	0.053
e	0.65 BSC			0.026 BSC		
L	0.26	0.36	0.46	0.010	0.014	0.018
L2	0.15 BSC			0.006 BSC		
aaa	0.15			0.01		
bbb	0.30			0.01		
ccc	0.10			0.00		
ddd	0.10			0.00		

8.SOLDERING FOOTPRINT



DISCLAIMER

- Curve guarantee in the specification. The curve of test items with electric parameter is used as quality guarantee. The curve of test items without electric parameter is used as reference only.
- Before you use our Products for new Project, you are requested to carefully read this document and fully understand its contents. LRC shall not be in any way responsible or liable for failure, malfunction or accident arising from the use of any LRC's Products against warning, caution or note contained in this document.
- All information contained in this document is current as of the issuing date and subject to change without any prior notice. Before purchasing or using LRC's Products, please confirm the latest information with a LRC sales representative.