

MOSFET Silicon N-Channel MOS

1. Applications

Soft Switching Boost PFC switch, Half bridge or Asymmetric half bridge or Series resonance half bridge and full bridge topologies.
phase-shift-bridge(ZVS), LLC Application-Server Power, Telecom Power, EV Charging, Solar inverter.



2. Features

Low drain-source on-resistance: $R_{DS(ON)} = 0.080\Omega$ (typ.)
Easy to control Gate switching
Enhancement mode: $V_{th} = 3$ to 5V




Table 1 Key Performance Parameters

Parameter	Value	Unit
$V_{DS @ T_{j,max}}$	650	V
$R_{DS(on),max}$	90	$m\Omega$
$Q_{g,typ}$	65	nC
$I_{D,pulse}$	141	A
Body diode dv/dt	50	V/ns

3. Packaging and Internal Circuit

Part Name	Package	Marking
ASW60R090EFD	TO247	ASW60R090EFD
ASA60R090EFD	TO220F	ASA60R090EFD



1 Maximum ratings

at $T_j = 25^\circ\text{C}$, unless otherwise specified

Table 2 Maximum ratings

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Continuous drain current ¹⁾	I_D		-	47	A	$T_C=25^\circ\text{C}$
Pulsed drain current ²⁾	$I_{D,\text{pulse}}$	-	-	141	A	$T_C=25^\circ\text{C}$
Avalanche energy, single pulse	E_{AS}	-	-	5336	mJ	
MOSFET dv/dt ruggedness	dv/dt	-	-	59	V/ns	$V_{DS}=0\ldots 400\text{V}$
Gate source voltage (static)	V_{GS}	-20	-	20	V	static;
Gate source voltage (dynamic)	V_{GS}	-30	-	30	V	AC ($f > 1 \text{ Hz}$)
Power dissipation(TO220F)	P_{tot}	-	-	34	W	$T_C=25^\circ\text{C}$
Power dissipation(TO247)	P_{tot}	-	-	391	W	$T_C=25^\circ\text{C}$
Storage temperature	T_{stg}	-55	-	150	°C	
Operating junction temperature	T_j	-55	-	150	°C	
Reverse diode dv/dt ³⁾	dv/dt	-	-	50	V/ns	$V_{DS}=0\ldots 400\text{V}, I_{SD} \leq 48\text{A}, T_j=25^\circ\text{C}$ see table 8

¹⁾Limited by $T_{j,\text{max}}$. Maximum Duty Cycle D = 0.50

²⁾Pulse width t_p limited by $T_{j,\text{max}}$

³⁾Identical low side and high side switch with identical R_G

re/ease

2 Thermal characteristics

Table 3 Thermal characteristics(TO220F)

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Thermal resistance, junction - case	R_{thJC}	-	-	3.65	°C/W	-
Thermal resistance, junction - ambient	R_{thJA}	-	-	80	°C/W	device on PCB, minimal footprint

Thermal characteristics (TO247)

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Thermal resistance, junction - case	R_{thJC}	-	-	0.32	°C/W	-
Thermal resistance, junction - ambient	R_{thJA}	-	-	62	°C/W	device on PCB, minimal footprint

release

3 Electrical characteristics

at $T_j=25^\circ\text{C}$, unless otherwise specified

Table 4 Static characteristics

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Drain-source breakdown voltage	$V_{(\text{BR})\text{DSS}}$	605	-	-	V	$V_{\text{GS}}=0\text{V}, I_{\text{D}}=10\text{mA}$
Gate threshold voltage	$V_{(\text{GS})\text{th}}$	3		5	V	$V_{\text{DS}}=V_{\text{GS}}, I_{\text{D}}=250\mu\text{A}$
Zero gate voltage drain current	I_{DSS}	-	-	5	μA	$V_{\text{DS}}=600\text{V}, V_{\text{GS}}=0\text{V}, T_j=25^\circ\text{C}$
Gate-source leakage current	I_{GSS}	-	-	100	nA	$V_{\text{GS}}=30\text{V}, V_{\text{DS}}=0\text{V}$
Drain-source on-state resistance	$R_{\text{DS}(\text{on})}$	-	0.080	0.090	Ω	$V_{\text{GS}}=10\text{V}, I_{\text{D}}=20\text{A}, T_j=25^\circ\text{C}$
Gate resistance (Intrinsic)	R_{G}	-	14	-	Ω	$f=1\text{MHz}$, open drain

Table 5 Dynamic characteristics

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Input capacitance	C_{iss}	-	4799	-	pF	$V_{\text{GS}}=0\text{V}, V_{\text{DS}}=50\text{V}, f=10\text{kHz}$
Output capacitance	C_{oss}	-	482	-	pF	$V_{\text{GS}}=0\text{V}, V_{\text{DS}}=50\text{V}, f=10\text{kHz}$
Reverse transfer capacitance	C_{rss}	-	4.6	-	pF	$V_{\text{GS}}=0\text{V}, V_{\text{DS}}=50\text{V}, f=10\text{kHz}$
Turn-on delay time	$t_{\text{d}(\text{on})}$	-	38.8	-	ns	$V_{\text{DD}}=400\text{V}, V_{\text{GS}}=13\text{V}, I_{\text{D}}=25.8\text{A}$ $R_{\text{G}}=1.7\Omega$; see table 9
Rise time	t_{r}	-	26.8	-	ns	$V_{\text{DD}}=400\text{V}, V_{\text{GS}}=13\text{V}, I_{\text{D}}=25.8\text{A}$ $R_{\text{G}}=1.7\Omega$; see table 9
Turn-off delay time	$t_{\text{d}(\text{off})}$	-	134.8	-	ns	$V_{\text{DD}}=400\text{V}, V_{\text{GS}}=13\text{V}, I_{\text{D}}=25.8\text{A}$ $R_{\text{G}}=1.7\Omega$; see table 9
Fall time	t_{f}	-	20	-	ns	$V_{\text{DD}}=400\text{V}, V_{\text{GS}}=13\text{V}, I_{\text{D}}=25.8\text{A}$ $R_{\text{G}}=1.7\Omega$; see table 9

Table 6 Gate charge characteristics




Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Gate to source charge	Q_{gs}	-	20	-	nC	$V_{\text{DD}}=400\text{V}, I_{\text{D}}=25.8\text{A}, V_{\text{GS}}=0 \text{ to } 10\text{V}$
Gate to drain charge	Q_{gd}	-	24	-	nC	$V_{\text{DD}}=400\text{V}, I_{\text{D}}=25.8\text{A}, V_{\text{GS}}=0 \text{ to } 10\text{V}$
Gate charge total	Q_{g}	-	65	-	nC	$V_{\text{DD}}=400\text{V}, I_{\text{D}}=25.8\text{A}, V_{\text{GS}}=0 \text{ to } 10\text{V}$
Gate plateau voltage	V_{plateau}	-	7.4	-	V	$V_{\text{DD}}=400\text{V}, I_{\text{D}}=25.8\text{A}, V_{\text{GS}}=0 \text{ to } 10\text{V}$

Table 7 Reverse diode characteristics

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Diode forward voltage	V_{SD}	-	0.66	-	V	$V_{GS}=0V, I_F=1A, T_j=25^\circ C$
Reverse recovery time	t_{rr}	-	120.8	-	ns	$V_r=400V, I_F=9.6A, dI/dt=100A/\mu s$ see table 8
Reverse recovery charge	Q_{rr}	-	0.7	-	μC	$V_r=400V, I_F=9.6A, dI/dt=100A/\mu s$ see table 8
Peak reverse recovery current	I_{rrm}	-	11.3	-	A	$V_r=400V, I_F=9.6A, dI/dt=100A/\mu s$ see table 8

re/re/ease

4 Test Circuits

Table 8 Diode characteristics

Table 9 Switching times

Table 10 Unclamped inductive load


5 Package Outlines

TO-220F

单位: mm




Figure1: Outline PG-T0220F




Figure2: Outline PG-T0247

Revision History

Revision	Date	Subjects (major changes since last revision)
0.1	2019-05-21	Preliminary version
1.0	2019-11-07	Fine tune outline and add Crss test data.etc
1.1	2020-03-18	Change part name for revision history
1.2	2020-03-23	Add part name "ASA60R090EFD"

release