






MAPX	MODIFICATION	DATE




- NOTES:
- MATERIAL:  
 MOLDING: LCP UL94 V-0  
 CONTACT: COPPER ALLOY.  
 GOLD PLATED Min ON CONTACT AREA, 100u"  
 Min TIN (LEAD FREE) ON SOLDER AREA,  
 SHELL: SUS304-H, T=0.30±0.03mm  
 50u" NICKEL PLATING OVER ALL.  
 SHILD: SUS304-H, T=0.12±0.03mm
  - MECHANICAL:  
 INSERTION: 5~20N.  
 EXTRACTION: 8~20N AFTER TEST.  
 DURABILITY: 10000 CYCLES
  - ELECTRICAL:  
 CURRENT: 5A FOR VBUS;  
 1.25A FOR GND PIN.  
 0.25A FOR OTHER.  
 VOLTAGE: 20 V MAX  
 WITHSTANDING VOLTAGE: 100V AC R.M.S.  
 CONTACT RESISTANCE: 40mΩ MAX.  
 INSULATION RESISTANCE: 100MΩ MIN.
  - ENVIRONMENTAL  
 TEMPERATURE RANGE -25°C ~ +85°C



产品图			
PRODUCT CHART DWG			
公差一览表			
TOLERANCE UNLESS OTHERWISE			
X.	±0.25	X.	±5.°
.X	±0.20	.X	±2.°
.XX	±0.15	.XX	±1.°
.XXX	±0.05	.XXX	±0.5°

# 深圳市精拓金电子有限公司

单位	MM	制图	邱建辉	制图料号	918-118A2021S40000
比例	1:1	审核	郭治富	产品名称	TYPE-C3. 1公头12. 5/15. 5沉板1. 3
日期	2016. 08. 04	核准	黄国荣	产品NO.	两脚插板双排SMT/LCP黑胶24PIN
UNIT		DRAWING		角法	版本
SCALE		CHECK		角法	YBR
DATE		APPD		角法	AO




USB TYPE-C FULL-FEATURED RECEPTACLE INTERFACE PIN ASSIGNMENTS



PIN	Signal Name	Description	PIN	Signal Name	Description
A1	GND	Ground return	B12	GND	Ground return
A2	SSTXp1	Positive half of first SuperSpeed TX differential pair	B11	SSRXp1	Positive half of first SuperSpeed RX differential pair
A3	SSTXn1	Negative half of first SuperSpeed TX differential pair	B10	SSRXn1	Negative half of first SuperSpeed RX differential pair
A4	Vbus	Bus Power	B9	Vbus	Bus Power
A5	CC1	Configuration Channel	B8	SBU2	Sideband Use (SBU)
A6	Dp1	Positive half of the USB 2.0 differential pair-Position 1	B7	Dn2	Negative half of the USB 2.0 differential pair-Position 2
A7	Dn1	Negative half of the USB 2.0 differential pair-Position 1	B6	Dp2	Positive half of the USB 2.0 differential pair-Position 2
A8	SBU1	Sideband Use (SBU)	B5	CC2	Configuration Channel
A9	Vbus	Bus Power	B4	Vbus	Bus Power
A10	SSRXn2	Negative half of second SuperSpeed RX differential pair	B3	SSTXn2	Negative half of second SuperSpeed TX differential pair
A11	SSRXp2	Positive half of second SuperSpeed RX differential pair	B2	SSTXp2	Positive half of second SuperSpeed TX differential pair
A12	GND	Ground return	B1	GND	Ground return

<b>产品图</b> PRODUCT CHART DWG		<b>深圳市精拓金电子有限公司</b>							
<b>公差一览表</b> TOLERANCE UNLESS OTHERWISE				单位 UNITS	MM	制图 DRAWING	邱建辉	制图料号 PRODUCT PART NO.	918-118A2021S40000
.X	± 0.25	.X	± 5.°	比例 SCALB	1:1	审核 CHECK	郭治富	产品名称 PRODUCT NO.	TYPE-C3.1公头12.5/15.5沉板1.3
.XX	± 0.20	.XX	± 2.°						两脚插板双排SMT/LCP黑胶24PIN
.XX	± 0.15	.XX	± 1.°	日期 DATE	2016.08.04	核准 APPD	黄国荣	角法 VIEW	版本 VER
.XXX	± 0.05	.XXX	± 0.5°						A0


MAPX	MODIFICATION	DATE




① 产品入载带示意图




② 卷盘贴标签示意图



③ 10盘产品叠层示意图




⑥ 外箱封箱示意图



⑤ 产品入外箱示意图

图四



④ 7盘产品入防水袋示意图

图三

包装说明:

1. 将检验好的成品;SMT朝下放入载带底部;每卷装1000PCS产品;具体如图一所示
2. 将包装好的产品;每盘必需贴上内标签;具体如图二所示
3. 将贴好内标签的产品每10盘叠一层装入防水袋中并加一包干燥剂;装好后将防水袋封好;具体如图三图四所示
4. 先将1pcs平卡放入纸箱底部;然后将装好产品的防水袋装入纸箱中;防水袋热熔封口,封口面需朝上;并将4PCS三角套分别装入4个角;如图五所示
5. 装好后将1pcs平卡放入纸箱最上面并封好纸箱及贴好相关标签;具体如图六所示;(产品包装的标签,如客户有要求,请按客户要求包装出货)
6. 载带前面留30PCS空格,后面留20PCS空格
7. COVER与CARRY剥离力:50-125g,速度:300mm/分钟左右,剥离角度:165°-180°

<p><b>产品图</b> PRODUCT CHART DWG</p>		<p><b>深圳市精拓金电子有限公司</b></p>							
<p>公差一览表 TOLERANCE UNLESS OTHERWISE</p>				<p>单位 UNITS</p>	<p>MM</p>	<p>制图 DRAWING</p>	<p>邱建辉</p>	<p>制图料号 PRODUCT PART NO.</p>	<p>918-118A2021S40000</p>
X.	± 0.25	X.	± 5.°	<p>比例 SCALE</p>	<p>1:1</p>	<p>审核 CHKD</p>	<p>郭治富</p>	<p>产品名称 PRODUCT NO.</p>	<p>TYPE-C3.1公头12.5/15.5沉板1.3两脚插板 双排SMT/LCP黑胶24PIN</p>
.X	± 0.20	.X	± 2.°						
.XX	± 0.15	.XX	± 1.°	<p>日期 DATE</p>	<p>2016.08.04</p>	<p>核准 APPD</p>	<p>黄国荣</p>	<p>角法 VIEW</p>	<p>版本 VER</p>
.XXX	± 0.05	.XXX	± 0.5°						<p>A0</p>