


1.View and size(视图及尺寸)


| Main technical indicators(主要技术指标)      |                                                                                                                       |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------|
| 1.Mating (插拔次数)                        | 5000                                                                                                                  |
| 2.Working Temperature (温度)             | -55~+250 ℃                                                                                                            |
| 3.IP Rating (防护级别)                     | IP68                                                                                                                  |
| 4.Resistance to vibration(抗振性)         | 15 g [10 Hz - 2000 Hz]                                                                                                |
| 5.盐雾                                   | 5% NaCl for 48 hours/5%NaCl雾气中 48小时                                                                                   |
| 6.Shock Resistance (抗冲击性)              | 100 g [ 6 ms]<br>100 g [ 6 毫秒]                                                                                        |
| 7.Shielding efficiency (min)屏蔽效率 (最小值) | 75 dB ( 10 MHz 时)                                                                                                     |
| 8.Shielding efficiency (min)屏蔽效率 (最小值) | 40 dB ( 1 GHz 时)                                                                                                      |
| 9.Diameter of socket end(插合端直径)        | φ0.5                                                                                                                  |
| 10.Testing Voltage (测试电压)              | 850V                                                                                                                  |
| 11.Working Voltage (工作电压)              | 650V                                                                                                                  |
| 12.Rated Current (额定电流)                | 2.5A                                                                                                                  |
| 13.Shell material(壳体材质)                | Brass (chromium plating) shell and chuck nut/( nickel plating) pin sleeve and middleware/黄铜 (镀铬) 外壳和夹头螺母/ (镀镍)插销套和中间件 |
| 14.Pin Material(插针材料)                  | Copper alloy gold plating(铜合金镀金)                                                                                      |
| 15.Insulator material(绝缘体材质)           | L:PPS P:PEEK                                                                                                          |

| Sum up(总结)                  |                                         |
|-----------------------------|-----------------------------------------|
| Series(系列)                  | T                                       |
| Shell style/model (外壳样式/型号) | ZGG:With a nut (post-fixed)带有一个螺母 (后固定) |
| Button (按键)                 | A button(一个按键)                          |
| Termination type (终止类型)     | Male solder(公焊锡)                        |
| Line diameter awg(线材直径)     | 34AWG-28AWG                             |
| Cable diameterφ (电缆直径)      | 0-0                                     |
| Matching parts(配件)          | TGG.0T.P06.CXADXXH                      |


|        | A      | B      | C√     | ANGLE   |       |
|--------|--------|--------|--------|---------|-------|
| 5-10   | ±0.02  | ±0.05  | ±0.1   | 0°-30°  | ±0.1° |
| 50-100 | ±0.1   | ±0.15  | ±0.2   | 61°-90° | ±0.5° |
| 50-100 | ±0.15  | ±0.2   | ±0.25  |         |       |
| 100-   | ±0.15% | ±0.20% | ±0.25% |         |       |




|    | A    | L    | E      | S1   | S2   |
|----|------|------|--------|------|------|
| MM | φ12  | 14.5 | M9*0.6 | 8.2  | 11   |
| in | 0.47 | 0.57 |        | 0.32 | 0.43 |




Welded surface  
(焊接面)



Pane hole size  
(面板开孔尺寸)



(Welded mother adhesive core)  
焊接型母胶芯



Positive view of the socket  
(插座正视图)

Model(型号) ZG G.0T.P06.C X L  
Positioning pin(定位销)  
Series(系列)  
Needle core configuration(针芯配置)  
Outer casing(外壳)  
Insulator(绝缘体)  
Needle core(针芯)

|                                  |  |          |                                      |               |          |                                        |
|----------------------------------|--|----------|--------------------------------------|---------------|----------|----------------------------------------|
| DESIGNED (设计)                    |  | DATE(日期) |                                      | SCALE(比例)     | N/A(不适用) | MODEL TYPE<br>型号类型: ZGG.0T.P06.CXL     |
| CHECKED (校对)                     |  | DATE(日期) |                                      | VIEW(视图)      |          | PART NO. 0T6-core socket<br>名称: 0T6芯插座 |
| APPROVED (审核)                    |  | DATE(日期) |                                      | UNIT(单位)      | MM       | DWG NO.:                               |
| REVISIONS                        |  |          |                                      | MATERIAL (材料) |          |                                        |
| www.helloxkb.com www.helloxkb.cn |  |          | XKB INDUSTRIAL PRECISION CO.,LIMITED |               |          | WEIGHT(重量) SHEET(表) REVISION(修订)       |
|                                  |  |          |                                      |               |          | 1/1 A0                                 |