


SS32 THRU SS310

SURFACE MOUNT SCHOTTKY BARRIER RECTIFIER

Reverse Voltage - 20 to 100 Volts Forward Current - 3.0 Amperes

DO-214AC/SMA	FEATURES
 Dimensions in inches and (millimeters)	MECHANICAL DATA Case: JEDEC DO-214AC molded plastic body Terminals: leads solderable per MIL-STD-750, Method 2026 Polarity: Color band denotes cathode end Mounting Position: Any Weight: 0.002 ounce, 0.07 grams

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.
Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

Catalog Number	SYMBOLS	SS32	SS33	SS34	SS35	SS36	SS38	SS310	UNITS
Maximum repetitive peak reverse voltage	V _{RRM}	20	30	40	50	60	80	100	VOLTS
Maximum RMS voltage	V _{RMS}	14	21	28	35	42	56	70	VOLTS
Maximum DC blocking voltage	V _{DC}	20	30	40	50	60	80	100	VOLTS
Maximum average forward rectified current at T _L (see fig.1)	I _(AV)	3.0							Amps
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I _{FSM}	100.0							Amps
Maximum instantaneous forward voltage at 3.0A	V _F	0.55			0.70		0.85		Volts
Maximum DC reverse current at rated DC blocking voltage	I _R	0.5							mA
T _A =25°C T _A =100°C		20					10		
Typical junction capacitance (NOTE 1)	C _J	500			300				pF
Typical thermal resistance (NOTE 2)	R _{θJA}	55.0							°C/W
Operating junction temperature range	T _J	-50 to +125					-50 to +150		°C
Storage temperature range	T _{STG}	-50 to +150							°C

Note: 1. Measured at 1MHz and applied reverse voltage of 4.0V D.C.
2. P.C.B. mounted with 0.2x0.2" (5.0x5.0mm) copper pad areas

SS32 THRU SS310

RATINGS AND CHARACTERISTIC CURVES SS32 THRU SS310

