


**20V N-CHANNEL ENHANCEMENT MODE MOSFET**
**MAIN CHARACTERISTICS**

$I_D$	8A
$V_{DSS}$	20V
$R_{DS(on)-typ}(@V_{GS}=4.5V)$	< 12mΩ (Type: 8.5 mΩ)


**Application**

- ◆ Battery protection
- ◆ Load switch
- ◆ Uninterruptible power supply


**Product Specification Classification**

Part Number	Package	Marking	Pack
YFW2320MI	SOT23-3L	2320	3000PCS/Tape

**Maximum Ratings at  $T_c=25^\circ\text{C}$  unless otherwise specified**

Characteristics	Symbols	Value	Units
Drain-Source Voltage	$V_{DS}$	20	V
Gate - Source Voltage	$V_{GS}$	$\pm 12$	V
Drain Current-Continuous	$I_D$	8	A
Drain Current-Continuous( $T_c=100^\circ\text{C}$ )	$I_{D(100^\circ\text{C})}$	4.5	A
Pulsed Drain Current	$I_{DM}$	75	A
Maximum Power Dissipation	$P_D$	12	W
Single pulse avalanche energy	$E_{AS}$	1	mJ
Operating Junction and Storage Temperature Range	$T_J, T_{STG}$	-55 to +150	°C
Thermal Resistance,Junction-to-Case	$R_{\theta JC}$	3.8	°C/W

**Maximum Ratings at T<sub>c</sub>=25°C unless otherwise specified**

<b>Characteristics</b>	<b>Test Condition</b>	<b>Symbols</b>	<b>Min</b>	<b>Typ</b>	<b>Max</b>	<b>Units</b>
Drain-Source Breakdown Voltage	V <sub>GS</sub> =0V, I <sub>D</sub> =250μA	BV <sub>DSS</sub>	20	22	-	V
Zero Gate Voltage Drain Current	V <sub>DS</sub> =20V, V <sub>GS</sub> =0V	I <sub>DSS</sub>	-	-	1	μA
Gate-Body Leakage Current	V <sub>GS</sub> =±12V, V <sub>DS</sub> =0V	I <sub>GSS</sub>	-	-	±100	nA
Gate -Threshold Voltage	V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =250μA	V <sub>GS(th)</sub>	0.5	0.65	1.2	V
Drain-Source On-State Resistance	V <sub>GS</sub> =4.5V, I <sub>D</sub> =6A	R <sub>DS(ON)</sub>	-	8.5	12	mΩ
	V <sub>GS</sub> =2.5V, I <sub>D</sub> =3A		-	10	15	
Forward Transconductance	V <sub>DS</sub> =5V, I <sub>D</sub> =20A	g <sub>FS</sub>	10	-	-	S
Input Capacitance	V <sub>DS</sub> =10V V <sub>GS</sub> =0V f=1.0MHz	C <sub>iss</sub>	-	625	-	pF
Output Capacitance		C <sub>oss</sub>	-	162	-	
Reverse Transfer Capacitance		C <sub>rss</sub>	-	105	-	
Turn-on delay time	V <sub>GS</sub> =10V V <sub>DS</sub> =10V R <sub>L</sub> =0.5Ω R <sub>GEN</sub> =3Ω	t <sub>d(on)</sub>	-	4.5	-	ns
Turn-on Rise Time		T <sub>r</sub>	-	9.2	-	
Turn-Off Delay Time		t <sub>d(OFF)</sub>	-	18.7	-	
Turn-Off Fall Time		t <sub>f</sub>	-	3.3	-	
Total Gate Charge	V <sub>GS</sub> =10V V <sub>DS</sub> =10V I <sub>D</sub> =20A	Q <sub>g</sub>	-	15	-	nC
Gate-Source Charge		Q <sub>gs</sub>	-	1.8	-	
Gate-Drain Charge		Q <sub>gd</sub>	-	2.8	-	
Diode Forward Voltage <sup>(Note 3)</sup>	V <sub>GS</sub> =0V, I <sub>S</sub> =25A	V <sub>SD</sub>	-	-	1.2	V
Diode Forward Current <sup>(Note 2)</sup>		I <sub>S</sub>	-	-	25	A
Reverse Recovery Time	T <sub>J</sub> = 25°C, I <sub>F</sub> = 20A di/dt = 100A/μs (Note3)	t <sub>rr</sub>	-	18	-	ns
Reverse Recovery Charge		Q <sub>rr</sub>	-	9.5	-	nC
Forward Turn-On Time	Intrinsic turn-on time is negligible (turn-on is dominated by LS+LD)	t <sub>on</sub>	-	-	-	-

Notes:

1. Repetitive Rating: Pulse width limited by maximum junction temperature.
2. Surface Mounted on FR4 Board, t ≤ 10 sec.
3. Pulse Test: Pulse Width ≤ 300μs, Duty Cycle ≤ 2%.
4. Guaranteed by design, not subject to production

Ratings and Characteristic Curves

Typical Characteristics




Figure 1 Output Characteristics




Figure 4 R<sub>dson</sub>-Junction Temperature




Figure 2 Transfer Characteristics




Figure 5 Gate Charge




Figure 3 R<sub>dson</sub>-Drain Current






Figure 6 Source- Drain Diode Forward


**Ratings and Characteristic Curves**




**Figure 7 Capacitance vs Vds**




**Figure 9 Power De-rating**



**Figure 8 Safe Operation Area**




**Figure 10 Current De-rating**



**Figure 11 Normalized Maximum Transient Thermal Impedance**

**Package Outline Dimensions Millimeters**

**SOT23-3L**



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
c	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E1	1.500	1.700	0.059	0.067
E	2.650	2.950	0.104	0.116
e	0.950(BSC)		0.037(BSC)	
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
$\theta$	0°	8°	0°	8°