



1.FIGURE AND DIMENSIONS(视图及尺寸)



端面

X1511H-XX-N0

XXXXXT-PXX-AXXXXXX-LXXX-XXXXXT-X

① ② ③ ④ ⑤ ⑥

- ① 系列 (Series No)
② 材质 (Material) :P-PSN(磷铜先冲后镀锡)
③ 线规线色 (Wire gauge line color) A:(AWG30-AWG24)
Circuit:R(red)/B (black) /Y (yellow) /G (green) /
L (blue) /P (purple) /YR (orange) /W (white)
④ 线长 (Line length) L:(可定制长度)
⑤ 系列 (Series No)
⑥ 正反接 (Positive and negative) Z(反接)/F (正接)

2. CIRCUIT DIAGRAM(接线图)

A	颜色	B
Circuit1	红色	Circuit4
Circuit2	黄色	Circuit3
Circuit3	黄色	Circuit2
Circuit4	黑色	Circuit1

3. MATERIAL(材料)

标志	料号	单用量	备注	总用量
1	X1511H-04-N0	2PCS		
2	X1511T-PSN	8PCS		
3	UL1007/24AWG. 红. 黑. 黄色	红. 黑色 各1PCS 黄色 2PCS	200MM	
总量				

⑥ 正反接 (Positive and negative) Z (反接)/F (正接)							DSND		SCALE: N/A	DRAWING NO.				
					ANGLAR	±5°				VIEW: 	X1511T-PSN-A24RYB-L200-X1511T-F			
Δx					L≤ 4	±0.2		DWN				PART NO.:		
Δx					4<L≤ 16	±0.3		CHKD			UNIT: mm/in	DWG NO.:		
Δx					16<L≤ 63	±0.4		APPD			SIZE: A4			
MARK	DESCRIPTION			DATE	REVISED	APPROVED		L> 63			±0.5			
REVISIONS							UNSPECIFIED TOLERANCES			XKB INDUSTRIAL PRECISION CO.,LIMITED				
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn											WEIGHT	SHEET	REVISION	
												1/1	A0	

					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5

REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						



XKB INDUSTRIAL PRECISION CO.,LIMITED