



1.FIGURE AND DIMENSIONS(视图及尺寸)



X2000H-XX-N0

XXXXXT-PXX-AXXXXXX-LXXX-XXXXXT-X
① ② ③ ④ ⑤ ⑥

- ① 系列 (Series No)
- ② 材质 (Material) :P-PSN(磷铜先冲后镀锡)
- ③ 线规线色 (Wire gauge line color) A:(AWG28-AWG22)
Circuit:R(red)/B (black) /Y (yellow) /G (green) /
L (blue) /P (purple) /YR (orange) /W (white)
- ④ 线长 (Line length) L:(可定制长度)
- ⑤ 系列 (Series No)
- ⑥ 正反接 (Positive and negative) Z(反接)/F (正接)

2. CIRCUIT DIAGRAM(接线图)

A	颜色	B
Circuit1	红色	Circuit9
Circuit2	黄色	Circuit8
Circuit3	黄色	Circuit7
Circuit4	黄色	Circuit6
Circuit5	黄色	Circuit5
Circuit6	黄色	Circuit4
Circuit7	黄色	Circuit3
Circuit8	黄色	Circuit2
Circuit9	黑色	Circuit1

3. MATERIAL(材料)

标志	料号	单用量	备注	总用量
1	X2000H-09-N0	2PCS		
2	X2000T-PSN	18PCS		
3	UL1007/24AWG. 红. 黑. 黄色	红黑各 1PCS/ 黄7PCS	300MM	
总量				

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK					L> 63	±0.5

REVISIONS

DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
------	---------	----------	------------------------

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

XKLB

DSND		SCALE: N/A	DRAWING NO. X2000T-PSN-A24RYYYYYYB-L300-X2000T-F
DWN		VIEW:	PART NO.:
CHKD		UNIT: mm/in	DWG NO.:
APPD		SIZE: A4	

XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET 1/1	REVISION A0
--------	--------------	----------------