













REV.	ECN NO OR DESCRIPTION	REVISED	DATE



建议胶圈尺寸



SPECIFICATION:

1.Material:

HOUSING&MOLDING:
HIGH TEMPERATURE RESISTANT PLASTIC,
UL94 V-0

CONTACTS:COPPER ALLOY T=0.15mm
IDDL CLIP:SUS301-1/2H,T=0.15mm
SHELL-1:SUS304, T=0.30mm
SHELL-2:SUS304, T=0.20mm

2.Mechanical:

2.1.Mating force:0.5~2.0kgf.
2.2.UNMATING FORCE:0.8~2.0kgf.
0.6~2.0kgf AFTER DURABILITY TEST;
2.3.Durability:10000 Cycles;

3.Electrical:

3.1.Current Rating:3A Max.;
3.2.Voltage Rating:20V Max.;
3.3.Dielectric Withstanding voltage:100VAc;
3.4.Contact resistance:40m Ohms Max.;
3.5.Insulation Resistance:100M Ohms Min.;

4.Environmental:

4.1.Operating temperature:-40°C~+85°C;
4.2.Wetting Temperature:265±5°C,5±0.5s
4.3.WATERPROOF: IPX7

A5	CC1	B5	CC2
A9	VBUS	B9	VBUS
A12	GND	B12	GND
PIN	SIGNAL	PIN	SIGNAL

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.50 X :±2°
X.X :±0.35 X.X :±1°
X.XX :±0.25






东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	TYPE	C 6PIN 防水母座板上型带塑胶柱		
DWN	xiong	PART NO.	MC-374FD	
CHKD	lee	SCALE:1:1	UNIT: mm	REV: A4
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4

CUSTOMER COPY



REV.	ECN NO OR DESCRIPTION	REVISED	DATE



说明:

1. 每卷前后各空16PCS, 尾部用美纹胶纸封住;
2. 将产品放满盘后, 再卷一圈保护带, 用美纹胶纸将其封住, 并贴上1Pcs物料标签;
3. 每10卷盘一叠共10000Pcs并装入1个外箱内;
4. 在搬运过程中要轻拿轻放;
5. 在运输中不可堆放过多(1.8M最高), 不可重压;
6. 跌落测试条件:
成品箱从1.2米高度自由落体(一角三棱六面):
 - a. 产品不可跑出下带凹槽;
 - b. 产品不可有摔伤, 变形;
 - c. 内包装材料不可严重破损.

NO.	NAME	SPEC	Q' TY
①	TYPE C RECEPTACLE		10000PCS/CARTON
②	CARRIER TAPE	W=24mm, T=0.35mm	1000PCS/PLATE
③	COVER TAPE	W=21.5mm	10PLATES/CARTON
④	REEL PLATE	330*100*24.4mm	10PCS/CARTON
⑤	RoHS LABEL		10PCS/CARTON
⑥	PRODUCT LABELER		10PCS/CARTON
⑦	CARTON	350*340*310mm	1PCS/PACKAGE
UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD	
DECIMALS: ANGLES:		TITLE TYPE C 6PIN 防水母座板上型带塑胶柱-包装图	
X :±0.50	X :±2°	DWN xiong	PART NO. MC-374FD
X.X :±0.35	X.X :±1°	CHKD lee	SCALE:1:1 UNIT: mm
X.XX :±0.25		APVD wang	SIZE: A4 SHEET:1OF 1 REV: A4
CUSTOMER COPY			