




Recommended P.C.Board
Hole Layout
(Tolerance:±0.05)



REV.	LOCAS	DESCRIPTION	DATE	DRAWN
01		繪圖產版	2006.07.25	丁敏
02	△	變更塑膠材料	17.04.2008	周禮軍
03	△	變更料號	2008.08.07	彭思城
04	△	變更圖號	2011.01.15	黃明霞

Specifications

Current Rating:1Amp
Insulation Resistance:1000MΩMin.
Dielectric Withstanding: 300VAC
Contact Resistance:20mΩMax.
Operating Temperature:—40°C to +105°C
Materials
Contact Material: Brass
Insulator Material: Polyester, UL 94V—0
△ LCP
All materials must meet Greenconn requirement for environment protection.



Ordering Information △

G PEA107 — XX XX A008 C 1 B X

No. of Pins per Row
02~33

Standard Plating
02=Gold Flash
Selective Plating
01=Tin
05=Gold Flash/Tin

Standard Packing
A=box
Selective Packing
C=Tube

格 菱 股 份 有 限 公 司
Greenconn Corporation

REV. 04 UNIT. mm SCALE. 1:1 PAGE. 1/1

GENERAL TOLERANCE	
X.±5.0°	X.±0.30
.X'±3.0°	.X±0.25
.XX'±2.0°	.XX±0.15
.XXX'±1.0°	.XXX±0.10

DESIGN: 黃明霞	DATE: 2011.01.15
CHECKED: 李新華	DATE: 2011.01.15
AUDITED: Lear	DATE: 2011.01.15

DWG. NO.	PART NO.
GPEA107-CA8CB	
GPEA107-XXXXA008C1BX	

TITLE:
1.27PIN HEADER SINGLE ROW DIP TYPE BASE 2.54H