



REV	LOCAS	DESCRIPTION	DRAW	DATE
01	NEW	INITIAL RELEASE	Junly	2010.08.16
05		ECN20120040	Huang	2012.09.26
06		ADD LOGO	Wang	2014.03.17



NOTES:

- MATERIAL:
 - Housing:High Temperature Thermoplastic UL94V-0; Color Black.
 - Terminal:Copper Alloy.
 - Nail:Stainless Steel
- SPECIALITY:
 - Rated current:2.0A
 - Rated voltage:30V
 - Contact Resistance:50mΩ MAX
 - Insulation Resistance:100MΩ MIN
 - Dielectric withstanding voltage: 250V AC.
 - Solder ability:245±5℃, 5±0.5s.
 - Durability:5000 Cycles Min.
 - Operating condition:Temperature: -30℃~+80℃; Humidity: 80% R.H MAX

Ordering Information



PART No.	DIM A	DIM B	PART No.	DIM A	DIM B
BA0306300450-26	4.50	3.00	BA0307300600-26	6.00	4.50
BA0306300500-26	5.00	3.50	BA0307300620-26	6.20	4.70
BA0306300550-26	5.50	4.00			

QUADRANT POINT TANGENCY POINT INTERSECTION POINT	 D-CHAIN DongGuan D-CHAIN Precision Components CO, Ltd				
UNLESS OTHERWISE SPECIFIED, TOLERANCE: X. ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAR ±3°	DESING	Huang	DATE	2012.09.26	TITLE: 3PIN BATTERY PH:3.00mm SMT TYPE WITH 2 POST
	CHECKED	Andy.L	DATE	2012.09.26	
	APPROVED	Andy.L	DATE	2012.09.26	
	PART NO:	BA0306300XXX-26		REV:	06
	DRAWING NO:	DQBA0306300450-26		SCALE:	5:1
				UNIT:	mm
				SIZE:	A4
				SHEET:	1/1

