







DRAWING FOR CUSTOMER



NOTES:

1. ELECTRICAL CHARACTERISTICS
  - 1-1. CONTACT RESISTANCE: 60 Milliohms Max
  - 1-2. INSULATION RESISTANCE: 1,000 Megohms Min.
  - 1-3. DIELECTRIC WITHSTANDING VOLTAGE: 250V AC FOR 1 MINUTE.
2. MECHANICAL CHARACTERISTICS
  - 2-1. OPERATION TEMPERATURE RANGE: -25°C~+70°C
  - 2-2. DURABILITY: 3000 CYCLES
3. MATERIAL:
  - 3-1. HOUSING: THERMOPLASTIC,UL 94-V0
  - 3-2. TERMINAL: PHOSPHOR BRONZE,T=0.10
  - 3-3. SHELL: STAINLESS STEEL,T=0.10
4. FINISHED:
  - 4-1. TERMINAL: Ni PLATED UNDER,Au PLATED ON CONTACT AREA,G/F PLATED ON SOLDER TAIL
  - 4-2. SHELL: Ni PLATED UNDER,G/F PLATED ON SOLDER TAIL

NANO SIM P/N	PIN NAME
P1	VCC
P2	RST
P3	CLK
P5	GND
P6	VPP
P7	I/O
G1	SWITCH

REV	ECN NUMBER	DESCRIPTION	DRAWN	DATE
A				

	GENERAL TOLERANCE		SCALE	1:1	DRAWN BY	DATE	DWG NO.	ZX-NSIM-481.25J	TITLE	REV
	XX. ±0.30	XXX. ° ±4°	UNIT	mm	CHECKED BY	DATE				
	X. ±0.25	XX. ° ±3°	SIZE	A4	APPROVED BY	DATE	PART NO.	SHEET		
	.X ±0.20	X. ° ±2°							1/1	