



客户编码		发行日期	2023/3/22																						
客户物料编码		客户规格型号	8*10-56UH-0.4线																						
样如物料编码	XR8*10-560K-L	样如规格型号	XR8*10-560K-L																						
送样数量	0PCS	送样日期	2023/3/22																						
外观尺寸 mm		<table border="1"> <tr> <td>A</td> <td>10.0 MAX</td> <td>E</td> <td>5.0±0.5</td> </tr> <tr> <td>B</td> <td>13.0 MAX</td> <td></td> <td></td> </tr> <tr> <td>C</td> <td>0.6±0.1</td> <td></td> <td></td> </tr> <tr> <td>D</td> <td>15.0±2.0</td> <td></td> <td></td> </tr> <tr> <td>标识</td> <td colspan="3"></td> </tr> </table>				A	10.0 MAX	E	5.0±0.5	B	13.0 MAX			C	0.6±0.1			D	15.0±2.0			标识			
A	10.0 MAX	E	5.0±0.5																						
B	13.0 MAX																								
C	0.6±0.1																								
D	15.0±2.0																								
标识																									
 正视图 FRONT VIEW		 顶视图 TOP VIEW		 底视图 BOTTOM VIEW																					
		 原理图																							

绕线结构表						
绕组	起始	结束	漆包线	圈数	绕制方式	
N1	S	F	2UEW-0.40mm	40.5TS	圈数参考	平整密绕

注意事项
 1、起线，收线入磁芯槽口 2、绕线要均匀平整，不能大小边 3、用黑色少字套管

测试项目	电性范围	测试条件	测试仪器	参考值
电感量L	56uH±10%	at 25℃ 1KHz/0.25V	TH2829A	56.70
直流电阻DCR	0.15Ω MAX	at 25℃ 1KHz/0.25V	TH2829A	0.11
饱和电流Isat	L ≥ L0*90%	at 25℃ DC 1.1A 1KHz/0.25V	TH2829A	

物料	规格型号	备注	生产厂家	用量
套管	Φ8*12.5mm UL黑色扁管		XINGQI	m
	Φ8.5mm UL黑色扁管		XINGQI	m
磁芯	R250 DR2W8*10 4-6-5	镁锌材质	LIANXING	K
漆包线	2UEW(155) 0.40mm		GANYUE	Kg
接脚胶	FK661 黑胶 无卤		QI FU	Kg
无铅锡	无铅锡条		SONGBEN	Kg

作业流程				
------	--	--	--	--

产品包装				
包装代码				
包装标识				
包装物料				
包装尺寸				
包装说明				

标识示意图		包装示意图	

制表	黄禾香
审核	饶平
确认	钟翠兰