



Fang cheng Electronics(Dong guan) Co,LTD
SPECIFICATION FOR APPROVAL

CUSTOMER:
Part Number : SMD CURREN TRANSFORMERS
CUSTOMER Number:
CUSTOMER Part :
Fangcheng part : FC-SCT6.0(100:1)-801-30A-S
DATE: 2023-1-29
REV: 01



Made in fangcheng:

CUSTOMER APPROD:

prepad	cheed	Approd
<i>Huang-ming</i>	<i>Liu-fang</i>	<i>Yuag-le</i>

prepad	cheed	Approd

THE INFORMATION CONTAINED IN THIS DOCUMENT IS OF A PROPRIETARY NATURE AND IS INTENDED TO BE KEPT CONFIDENTIAL BETWEEN THE SENDER AND THE INTENDED RECIPIENT. IT MAY NOT BE REPRODUCED OR USED WITHOUT EXPRESS WRITTEN PERMISSION OF FC TECHNOLOGIES, OR FC



Fangcheng Electronics (Dongguan) Co., Ltd.

Tel: +86 0769-82988010

Fax: +86 0769-82988065

E-mail: yhl@fangchengcoils.com

URL: www.fangchengcoils.com

Address: Building 3, Jinmei Technology Park, No.16 Huanchang West Road, Changping Town, Dongguan City

Fangcheng Electronics (China-Taiwan) Office

Address: No. 31, MRT Road, Zhonghe District, New Taipei City

Tel: +8869-983491379



本文件中包含的信息具有专有性质，旨在对发件人和目标收件人之间保密。未经方成（FC）技术或FC明确书面许可，不得复制或提供给第三方使用，TKS

Notice of Use

For the parameters not prescribed in the *Specification for Approval*, please refer to the following standards or the relative industry standards.

1. Product in packing storage condition : temperature 540, RH70%.
2. A storage of - F C -Electronic products for longer than 12 months is not recommended, Within other effects, the terminals may suffer degradation, resulting in bad solderability. Therefore, all products shall be used within the period of 12 months based on the day of shipment.
3. Do not keep products in unsuitable storage conditions, such as areas susceptible to high temperatures, high humidity, dust or corrosion.
- 4 Always handle products with care.
- 5 Don't touch electrodes directly with bare hands as oil secretions may inhibit soldering.
Always ensure optimum conditions for soldering.
- 6 When this product will be used on a similar or new project to the original one, sometimes it might be unable to satisfy the specifications due to different condition of usage.
- 7 This inductor itself does not have any protective function in abnormal condition, such as overload, short-circuit, open-circuit conditions, etc. Therefore, it shall be confirmed that there is no risk of smoke, fire, dielectric withstand voltage, insulation resistance, etc., or use in abnormal conditions protective devices or protection circuit in the end product.
- 8 Hi-Pot test with higher voltage than spec value will damage insulating material and shorten its life.

IPC 020D Joint Industry standard

IEC1007 《Transformer and inductors for use in electronic and telecommunication equipment—Measuring methods and test procedures》

(ROHS or other environmental request)




Prepad <i>zhangli</i>	Checd <i>Wu-pen</i>	Approd <i>David-yuan</i>
------------------------------	----------------------------	---------------------------------

5. WINDING SPECIFICATION

NO.	线圈名称	起始引脚号	结尾引脚号	导线规格	匝数	绝缘层
1	N1	1	2	Φ0.07mm	100	2Ts
2	N2	5	6	δ=0.20mm 紫铜	1	

5.1 BOM



No.	Part name	Materials	UL No.
1	Bobbin	LCP E4008 (94V-0)	E54705 or Equivalent
2	Core	Mn-Zn Ferrite	N/A
3	Clip	C1100H	N/A
4	Wire	Polyurethane enameled wire	E258243 or Equivalent
5	Tape	Polyimide	E328315/ E165111 or Equivalent
6	Epoxy	Epoxy resin	N/A
7	Terminal	C1100H	N/A
	Solder	Sn/Ag/Cu	N/A

本产品符合RoHS 2.0 (2011/65/EU)



Prepad <i>zhangli</i>	Checd <i>Yi-pen</i>	Approd <i>David-yuan</i>
------------------------------	----------------------------	---------------------------------


6. Reliability and test condition:

Test item	test condition	Remark
Cold Operating Test	GB2423.1 Ad	
Heat Operating Test	GB2423.2 Bd	
Cold Storage Test	GB2423.1 Ab	
Heat Storage Test	GB2423.2 Bb	
Steady Damp Heat Test	GB2423.3 Cb	
Circular Damp Heat Test	GB2423.4 Db	
Temperature Cycling Test	GB2423.22 Nb	
Temperature Shock Test	GB2423.22 Na	
Vibration Test	GB2423.10~15 Fc, Fdb	
Mechanical Shock Test (Bump)	GB2423.5 Eb	
Free Fall Test	GB2423.8 Ed	
Solderability	GJB360A-96	
High Temperature Step Stress Test	Enhancement Test Specifications	
Low Temperature Step Stress Test		
High-speed Thermal Cycling		
Limit Vibration		
Composite Stress		
Highly-Accelerated Temperature and Humidity Stress Test (HAST) (



Prepad <i>zhangli</i>	Checkd <i>Wu-pen</i>	Approd <i>David-yuan</i>
-------------------------------------	------------------------------------	--

7. Soldering Specification: 元器件的推荐焊接方式是回流焊



	Package Thickness 封装厚度	Package Volume 封装体积		
		<350 mm ³	350~2000 mm ³	>2000 mm ³
PB-Free Assembly 无铅装配	<1.6mm	260°C	260°C	260°C
	1.6~2.5mm	260°C	250°C	245°C
	≥2.5mm	250°C	245°C	245°C

※ Reflow is referred to standard IPC/JEDEC J-STD-020D.
回流焊参照标准 IPC/JEDEC J-STD-020D。



7.1 高温耐热性：在260°C的熔融钎料中，停留时间不少于10 秒，无质量问题。



7.2 返修温度和时间温度：350 度；时间：不少于5 秒。

7.3 焊接次数：元器件能承受的焊接次数不少于5 次

Prepad <i>zhangli</i>	Checd <i>W-pen</i>	Approd <i>David-yuan</i>
--------------------------	-----------------------	-----------------------------

8.1 包装:

- 1) 包装箱上应标明产品型号、名称、数量、出厂日期、承制方名称及出厂检验章;
 - 2) 货物运达客户方后, 包装箱封条应完好, 箱体无破损、开裂等现象;
 - 3) 电感用木箱或其他材料包装, 方便拆卸, 四周用软性材料填充;
- 数量: 1000PCS/R



Reel size	QTY (pcs/reel)	A mm	B mm	C mm	D mm	G mm	T mm
113"	1000	330	100	13.5±0.5	16.0±0.3	16.8 ±0.5	18.8±2.0

8.2 外观:

- 1) 产品应有合格证和耐擦防水洗标签, 应注明型号、规格;
- 2) 产品外观整洁, 应无破损、划伤;



8.3 检验:

- 1) 产品生产中必须全数进行电气性能, 抗电强度检测; 箱内应有 100%电气性能合格保证书或检测报告;
- 2) 产品出货前按批次, 必须根据承认书按国家行业标准进行抽样检验, 合格后出具出厂检验报告, 记录抽样测试数据, 在每批次包装尾箱中放置一份; 检验报告须注明 100%耐压测试合格。注: 批次按定单号发货为准

<p>Prepad</p> <p style="text-align: center;"><i>zhangli</i></p>	<p>Checkd</p> <p style="text-align: center;"><i>Wu-pen</i></p>	<p>Approd</p> <p style="text-align: center;"><i>David-yuan</i></p>
---	--	--