



Specifications:

规格:

Voltage rating:150V AC/DC
 额定电压: 150V AC/DC
 Current rating:1A AC/DC
 额定电流: 1A AC/DC
 Withstanding voltage:500V AC/minute
 耐受电压: 500V AC/分钟
 Temperature range:-25°C~+85°C
 温度范围: -25°C~+85°C
 Insulation resistance:≥500MΩ min
 绝缘电阻: ≥500MΩ Min
 Contact resistance:≤30mΩ Max
 接触电阻: ≤30mΩ Max

X9812 W V S - 2xXX - 6T V01

① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:V-Stright 180°
- 4.Welding Way:S-SMT
- 5.Row No.Pin No:XX-2x05~2x25P
- 6.Material:6T-PA6T UL 94V-0 Natural
CAP:PA6T UL 94V-0 Natural
- 7.Plating:V01-Gold Flash

Poles	Dimensions(mm)	
	A	B
2x02	1.25	8.75
2x05	5.00	12.50
2x06	6.25	13.75
2x07	7.50	15.00
2x10	11.25	18.75
2x12	13.75	21.25
2x15	17.50	25.00
2x20	23.75	31.25

X9812WVS-2xXX-6TV01	PA6T	Brass	X9812H
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND		SCALE: N/A	MODEL TYPE: 1.25mm Crimp Style Connector
DWN		VIEW:	PART NO.: X9812WVS-2xXX-6TV01
CHKD		UNIT: mm/in	DWG NO.: X-X9812WVS-2xXX-6TV01
APPD		SIZE: A4	WEIGHT SHEET REVISION 1/1 A0



XKB INDUSTRIAL PRECISION CO.,LIMITED

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	

广东星坤科技股份有限公司

姓名	日期
数量	日期
文件	工程章