



1.FIGURE AND DIMENSIONS(视图及尺寸)



端面

X1002H-XXL-NOHF

XXXXXT-PXX-AXXXXXX-LXXX-XXXXXT-X

① ② ③ ④ ⑤ ⑥

- ① 系列 (Series No)
- ② 材质 (Material) :P-PSN(磷铜先冲后镀锡)
- ③ 线规线色 (Wire gauge line color) A:(AWG32-AWG28)
Circuit:R(red)/B (black) /Y (yellow) /G (green) /
L (blue) /P (purple) /YR (orange) /W (white)
- ④ 线长 (Line length) L:(可定制长度)
- ⑤ 系列 (Series No)
- ⑥ 正反接 (Positive and negative) Z(反接)/F (正接)

2. CIRCUIT DIAGRAM(接线图)

A	颜色	B
Circuit1	红色	Circuit7
Circuit2	黄色	Circuit6
Circuit3	黄色	Circuit5
Circuit4	黄色	Circuit4
Circuit5	黄色	Circuit3
Circuit6	黄色	Circuit2
Circuit7	黑色	Circuit1

3. MATERIAL(材料)

标志	料号	单用量	备注	总用量
1	X1002H-07L-N OHF	2PCS		
2	X1002T-PSN2	14PCS		
3	UL1007/28AWG. 红. 黑. 黄色	红. 黑色 各1PCS 黄色 5PCS	200MM	
总量				

⑥ 正反接 (Positive and negative) Z(反接)/F (正接)						XKLB		DSND		SCALE: N/A	DRAWING NO.				
					ANGLAR			±5°	DWN		VIEW:	X1002LT-PSN-A28RYYYYYB-L200-X1002LT-F			
ΔX					L≤ 4			±0.2	CHKD		UNIT: mm/in	PART NO.:			
ΔX					4<L≤ 16			±0.3	APPD		SIZE: A4	DWG NO.:			
ΔX					16<L≤ 63			±0.4							
MARK	DESCRIPTION				DATE	REVISED	APPROVED	L> 63	±0.5						
REVISIONS						UNSPECIFIED TOLERANCES				XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn														1/1	A0