



NOTES 注释:

1. MATERIAL 材料:

1.1 HOUSING外壳: THERMOPLASTIC, HIGH TEMP.,
UL94V-0;
COLOR: SEE PART NO..

1.2 CONTACTS触点: COPPER ALLOY.

1.3 CLIP接线柱: COPPER ALLOY.

2. FINISH 饰面:

2.1 CONTACT触点:

SELECTEIVE GOLD PLATING ON CONTACT AREA.
100µ"MIN. MATTE TIN PLATING ON SOLDER TAILS,
50µ" MIN. NICKEL UNDERPLATING OVERALL.

X3196 W V - XX X - 46 V01
① ② ③ ④ ⑤ ⑥ ⑦

1.Series Nunber

2.Terminal form: W-Wafer

3.Welding Board Angle : V-Stright Angle 180°

4.No.of Pins: XX-280 Pin



5.Tail Length (DIM "E") / B Type:3.1mm ;
C Type:2.54mm

6.Plastic material: PA46 /PA9T UL94V-0

7.Contact Plating:V01-Gold Flash

V15-Gold 15u"

V30-Gold 30u"



SECTION:A-A

广东星坤科技股份有限公司

文件工程章


MARK, DESCRIPTION, DATE, REVISED, APPROVED

				ANGLAR	±5°
				L ≤ 4	±0.2
				4 < L ≤ 16	±0.3
				16 < L ≤ 63	±0.4
ITION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE:
DWN		VIEW:	PART NO.: X3196WV-XXX-46V01
CHKD		UNIT: mm/in	DWG NO.: X-X3196WV-XXX-46V01
APPD		SIZE: A4	WEIGHT
			SHEET 1/1
			REVISION A0



MARK	文件工程章	DES
------	-------	-----

日期					ANGLAR	±5°
					L ≤ 4	±0.2
					4 < L ≤ 16	±0.3
					16 < L ≤ 63	±0.4
DESCRIPTION		DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dq.cn						

XKLE

DSND		SCALE: N/A	MODEL TYPE:		
DWN		VIEW: 	PART NO.:		
CHKD		UNIT: mm/in	X3196WV-XXX-46V01		
APPD		SIZE: A4	DWG NO.:		
			X-X3196WV-XXX-46V01		
PRECISION CO., LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0