



^{2.} This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.



2

Data Sheet

Continued from the preceding page.

Packaging

Code	Packaging	Minimum Quantity		
D	180mm Paper Tape	15000		
В	Bulk(Bag)	500		

■ Rated Value (□: packaging code)

Part Number	Common Mode Impedance (at 100MHz/20°C)	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	DC Resistance	Operating Temperature Range
DLP0QSN600HL2	60ohm ±25%	50mA	5Vdc	100M ohm	12.5Vdc	3.8ohm±25%	-40 to +85°C
DLP0QSA070HL2	7ohm ±2ohm	100mA	5Vdc	100M ohm	12.5Vdc	0.7ohm±25%	-40 to +85°C
DLP0QSA150HL2	15ohm ±5ohm	100mA	5Vdc	100M ohm	12.5Vdc	0.8ohm±25%	-40 to +85°C
DLP0QSA350HL2	35ohm ±10ohm	100mA	5Vdc	100M ohm	12.5Vdc	2.20hm±25%	-40 to +85°C

Number of Circuit: 1

■ ①Caution/Notice

Do not use products beyond the rated current and rated voltage as this may create excessive heat and deteriorate the insulation resistance.

Notice

Solderability of Tin plating termination chip might be deteriorated when low temperature soldering profile where peak solder temperature is below the Tin melting point is used. Please confirm the solderability of Tin plating termination chip before use.

•This data sheet is applied for CHIP COMMON MODE CHOKE COIL used for General Electronics equipment for your design.

ANote:

1. This datasheet is downloaded from the website of Murata Manufacturing co., ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

