

APPLICABLE STANDARD		SPECIFICATIONS					
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C ⁽¹⁾	STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C ⁽²⁾			
	VOLTAGE	100 V AC	OPERATING HUMIDITY RANGE	40 % TO 80 %			
	CURRENT	0.4 A	STORAGE HUMIDITY RANGE	40 % TO 70 % ⁽²⁾			
CONSTRUCTION							
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.			<input checked="" type="checkbox"/> <input checked="" type="checkbox"/>		
MARKING	CONFIRMED VISUALLY.				<input checked="" type="checkbox"/> <input checked="" type="checkbox"/>		
ELECTRIC CHARACTERISTICS							
CONTACT RESISTANCE	100 mA (DC OR 1000 Hz).	45 mΩ MAX.			<input checked="" type="checkbox"/>		
CONTACT RESISTANCE	20 mV MAX, 1 mA(DC OR 1000Hz)	55 mΩ MAX.			<input checked="" type="checkbox"/>		
MILLIVOLT LEVEL METHOD							
INSULATION RESISTANCE	250 V DC.	100 MΩ MIN.			<input checked="" type="checkbox"/>		
VOLTAGE PROOF	300 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.			<input checked="" type="checkbox"/>		
MECHANICAL CHARACTERISTICS							
MECHANICAL OPERATION	50 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 55 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			<input checked="" type="checkbox"/>		
VIBRATION	FREQUENCY 10 TO 55 Hz, AMPLITUDE : 1.5 mm, AT 2 h FOR 3 DIRECTION.	① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② CONTACT RESISTANCE: 55 mΩ MAX.			<input checked="" type="checkbox"/>		
SHOCK	490 m/s ² , DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.	③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			<input checked="" type="checkbox"/>		
ENVIRONMENTAL CHARACTERISTICS							
DAMP HEAT (STEADY STATE)	EXPOSED AT 40±2 °C, 90 ~ 95 %, 96 h.	① CONTACT RESISTANCE: 55 mΩ MAX. ② INSULATION RESISTANCE: 100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			<input checked="" type="checkbox"/>		
RAPID CHANGE OF TEMPERATURE	TEMPERATURE-55→+15~+35→+85→+15~+35°C TIME 30 → 2~3 → 30 → 2~3 min UNDER 5 CYCLES.				<input checked="" type="checkbox"/>		
CORROSION SALT MIST	EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.	① CONTACT RESISTANCE: 55 mΩ MAX. ② NO HEAVY CORROSION.			<input checked="" type="checkbox"/>		
HYDROGEN SULPHIDE	EXPOSED IN 3 PPM FOR 96 h. (TEST STANDARD: JEIDA-38)				<input checked="" type="checkbox"/>		
RESISTANCE TO SOLDERING HEAT	1) REFLOW SOLDERING : 250 °C MAX, : 220 °C MIN, FOR 60 s 2) SOLDERING IRONS : 360 °C, FOR 5 s 	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.			<input checked="" type="checkbox"/>		
SOLDERABILITY  	SOLDERED AT SOLDER TEMPERATURE, 240 ± 3°C, FOR IMMERSION DURATION, 3 s.	A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.			<input checked="" type="checkbox"/>		
COUNT	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE		
 1	DIS-F-000293		KT. DOI	HS. OZAWA	05.07.28		
REMARK							
(1) TEMPERATURE RISE INCLUDED WHEN ENERGIZED. (2) THIS STORAGE INDICATES A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE THE BOARD MOUNTED. Unless otherwise specified, refer to JIS C 5402.							
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-150726-22		
	SPECIFICATION SHEET		PART NO.	FX8-*P-SV(92)			
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL578	 1/1		