

MLX90287 & MLX90297 SINGLE-COIL FAN DRIVERS

12V ROBUST FAN DRIVERS

MLX90287 & MLX90297

The MLX90287 & MLX90297 are the 2nd GEN of all-in-one single-coil fan drivers with highly sensitive hall sensor using AGC control for optimal low noise/high efficiency commutation control regardless of the magnetic field strength. The PWM input allows controlling the fan speed in combination with a number of resistor-configurable settings to adapt the speed curve to application specific requirements. Targeting low noise fan control in VGA card cooling applications, the GEN II low noise motor control features also have been leveraged in demanding home appliance, white goods, industrial and automotive cooling systems.

KEY FEATURES

- CertificationAECQ-100
- O Low BOM cost
 - Minimum discrete components
 - Single layer pcb, even half size possible
- Ø VGA speed curves

QUICK REFERENCE

Quick Reference	MLX90287	MLX90297	
Minimum speed	Configurable*	Configurable*	
Speed curve	Fixed	Configurable* 10%/20%/30%	
Average Fan current	< 450 mA	< 600 mA	
Motor Power	5 W	7 W	
Current limiting	No	Yes	
Soft start	Yes	Yes	
Soft switching	Yes	Yes	
Reverse polarity	Built-in	External diode	
Supply voltage range	[4.5V, 18V]	[3.3V, 18V]	
ESD-HBM**	7 kV	9 kV	

* Configurable by external resistor (Rvref, Rminsp, R1).

** Human Body Model according AEC-Q100-002 standard.



MLX90297 SCHEMATIC



FOR MORE INFORMATION: WWW.MELEXIS.COM/MLX90287 WWW.MELEXIS.COM/MLX90297



ORDERING INFORMATION

Order code*	Grade	Package	FG/RD	Current limit
MLX90287KZC-AAA-000	Industrial/Consumer	ZC: Straight leads SOIC8	FG	N/A
MLX90297KZC-AAF-108	Industrial/Consumer	ZC: Straight leads SOIC8	FG	800 mA
MLX90297KZC-ABF-108	Industrial/Consumer	ZC: Straight leads SOIC8	RD	800 mA
MLX90297KLW-AAF-109	Industrial/Consumer	LW: DFN10 3x3x1	FG	960 mA
MLX90297LLW-AAF-108	Automotive	LW: DFN10 3x3x1	FG	800 mA
MLX90297LLW-AAF-206	Automotive	LW: DFN10 3x3x1	FG	660 mA
MLX90297LLW-ABF-206	Automotive	LW: DFN10 3x3x1	RD	660 mA

* More ordering codes are available, please contact your sales representative for more information.

APPLICATION VISUALS







he above information is "as is" and believed to be correct and accurate. Melesis disclaims any and all fability in connection with or a raining out of the furnishing, application or use of the information or products any and all fability inducting without limitation special, consequential or incidental and any and all generatisms are used to the strain of the furnishing application or use of the information or products any and all fability inducting without limitation special, consequential or incidental any angle and all warranties express. Statutory, implicit or by description, inducing writerials of firsters for a pericular purpose, convintingement and meta-translity. Melessife reserves the right prime and without incide. Less should obtain the least variant of the statutory is a current. Users must further determine the suitability of a product for its application, including writeria of the suitability of a product for its application, including writeria of the suitability required and determine whether it is fit for a particular purpose. Export control regulations may apply and export might require a prior authorization from ompetent authorities. Melessify products are intereded for use in normal commercial applications. Unless otherwise agreed upon in writing, the productes are not designed, authorized or warranted to be suitable in applications requiring experiments. High-least or full accurate the suitability application and the super statutory and and the super statutory and the super statutory and the super statutory and and the super statutory and the super statutory and and commercial applications. Unless otherwise agreed upon in writing, the product devices if mort as a writing exploration forms and commercial applications. Super statutory and the super statutory