






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	NC	REDRAWN/REPLACES PREVIOUS	-	-	-
		RELEASE PER E.O. PI9542	12JUN2007	-	RDR
	A	REVISED PER E.O. PI9542	18MAY2010	-	RDR
	D	REVISED PER PCN E-20-009825	09JUL2020	PMV	IG



3-DIMENSIONAL VIEW



7. SECONDARY WEDGE LOCK SOLD SEPARATELY: W12P-XXXX.
(XXXX = ALL MODIFICATIONS)

6. RECOMMENDED SCREW: 6-32 [M4].
RECOMMENDED TORQUE: 20-25 IN-LB [2.26-2.82 Nm].

5. MATERIAL - HOUSING: PA66 GF15
GROMMET: VMO (ORANGE RED)

4. THIS RECEPTACLE MATES WITH DT06-12SX-XXXX PLUG.
(X = KEY ARR. A,B,C,D; XXXX = ALL MODIFICATIONS)
CONSULT FACTORY FOR MODIFICATIONS.

3. FOR CONTACT AND WIRE PERFORMANCE AND APPLICATION
CHARACTERISTICS, SEE ENVELOPE DRAWING 0425-015-0000.

2. DELETED

NOTES: 1. DELETED

CONTACT SIZE	MIN. INSUL O.D.	MAX. INSUL O.D.	WIRE RANGE [mm ²] REF ONLY
16	.088 [2.24]	.145 [3.68]	14-20 AWG [2.0-0.5]


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A MALAGON CHK R MCCORD APVD S BEARD	16MAY2007 14MAY2010 04MAY2010	TE Connectivity	
DIMENSIONS: INCHES[MM]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	108-151009	NAME 12 WAY RECEPTACLE W/ FLANGE-L012 MOD DT SERIES	
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.025 [0.64] 4 PLC ± ANGLES ±0° 30' 0"	APPLICATION SPEC	114-151009	SIZE A2	CAGE CODE 00779
MATERIAL 5	FINISH -	WEIGHT -	CUSTOMER DRAWING	DRAWING NO DT04-12PX-L012	RESTRICTED TO -
SCALE 2:1				SHEET 1	REV D

Technical drawing of a panel cutout showing dimensions and tolerances. The drawing includes a central rectangular cutout with rounded corners and four circular mounting holes at the corners. The dimensions are as follows:

- Overall width: 1.770 ± 0.003 [44.96 $\pm$ 0.07]
- Overall height: $.926 \pm 0.005$ [23.52 $\pm$ 0.12]
- Inner width: 1.647 ± 0.005 [41.83 $\pm$ 0.12]
- Inner height: $.940 \pm 0.003$ [23.88 $\pm$ 0.07]
- Corner radius: R.250 [6.35]
- Mounting hole diameter: $\varnothing .169 \pm 0.003$ [4.29 $\pm$ 0.07]
- Surface texture symbol: 6

RECOMMENDED PANEL CUTOUT

DT04-12PD-L012
KEY -D-
COLOR: BROWN



KEY - D -

1471-9 (3/13)