Product summary **MAYA-W1** series

Host-based multiradio modules with Wi-Fi 4 and Bluetooth 5.2

Small, flexible, dual-band Wi-Fi 4 and full-featured Bluetooth Low Energy 5.2 modules

- Wi-Fi 4 (802.11a/b/g/n) dual-band 2.4 and 5 GHz
- Operation modes: Access-point, Station, Wi-Fi direct (combinations)
- Dual-mode Bluetooth classic and Bluetooth Low Energy 5.2
- · Support for long range Bluetooth Low Energy and rate up to 2 Mbit/s
- Variants with PCB-antenna, U.FL connectors, and antenna pins
 - blox hlox 10.4 x 14.3 × 1.8 mm MAYA-W160 MAYA-W161



80

5

90

Product description

The MAYA-W1 series are host-based Wi-Fi 4 and Bluetooth 5.2 multiradio modules designed for a wide range of industrial applications, such as industrial automation and smart manufacturing, EV charging infrastructures, professional appliances, tracking and telematics, point-of-sale and ticketing machines, building automation, and healthcare. The modules are designed and built to meet the high reliability and quality requirements of such applications.

MAYA-W1 modules support the Wi-Fi 4 (802.11a/b/g/n) standard and deliver up to 150 Mbit/s data throughput. With dual-band 2.4/5 GHz and 40 MHz channel-width, the modules can work as a station with different types of access points, such as a simple access point, in P2P communication, or a combination of these. MAYA-W1 supports both Bluetooth classic and Bluetooth Low Energy 5.2.

At 10.4 x 14.3 mm, MAYA-W1 are among the most compact Wi-Fi dual-band SMD modules available in the market.

All u-blox modules undergo extensive gualification tests to ensure reliability over their life-time, and each module is fully tested before leaving the assembly line.

MAYA-W1 is based on the multiradio chip IW416 from NXP. **Key features**

- Variants with antenna pins, U.FL connectors and embedded PCB antenna
- Wi-Fi 4, dual-band, single stream, data rate up to 150 Mbit/s
- 20 and 40 MHz Wi-Fi channels
- Wi-Fi 802.11d/e/h/i/k/r/u/v/w
- Dual-mode Bluetooth version 5, supporting all features
- Temperature range -40 °C to +85 °C
- Security: WPA3, WPA2, TKIP/WPA, WEP (64/128 bit), WAPI, AES
- Supports up to 8 Stations in AP-mode
- Supports up to 16 Bluetooth Low Energy connections

		MAYA-W16	MAYA-W16	MAYA-W16
Grade		Σ	Σ	Σ
Automotive Professional Standard Radio		•	•	
Chip inside		NXP IW416		
Bluetooth qualification			v5.2	
Bluetooth profiles		HCI		
Bluetooth BR/EDR		•	•	•
Bluetooth Low Energy		•	•	•
Wi-Fi 4 IEEE 802.11 standards		a/b/g/n		
Wi-Fi frequency band [GHz]		2.4 and 5		
Bluetooth output power conducted [dBm]		10	10	10
Wi-Fi output power conducted [dBm]		18	18	18
Antenna type		U.FL	pin	pcb /pin
Number of antennas		2	2	1
OS support				
Android / Linux drivers (from u-blox)		•	•	•
RTOS (via NXP i.MX RT MCUs)		•	•	•
Interfaces				
High-speed UART (Bluetooth)		1	1	1
PCM, I2S (Bluetooth audio)		1	1	1
SDIO (Wi-Fi) [version]		3.0	3.0	3.0
Features		-	-	-
Micro Access Point [max connects]		8	8	8
Wi-Fi direct		·	•	•
WPA3		•	•	•
RF calibration in OTP		·	•	•
Programmed MAC address		•	•	•
pin = antenna pin	U.	FL = U.FL	antenna	connecto

pcb = internal PCB antenna

blox









MAYA-W1 series

Features

Wi-Fi standards	Wi-Fi 4 IEEE 802.11a/b/g/n IEEE 802.11d/e/h/i/k/r/u/v/w
Wi-Fi channels	2.4 GHz: 1-13 5 GHz: 36-165
Bluetooth	v5.2, class 1 and 2 transmission Bluetooth low energy and Bluetooth BR/EDR
Antennas	MAYA-W160: 2 U.FL connectors MAYA-W161: 2 antenna pins MAYA-W166: 1 embedded PCB antenna or pin
Output Tx-power	TBD
Security	128-bit AES hardware encryption

Software features

RF calibration	Available in on-board OTP memory
MAC addresses	Available in on-board OTP memory
Security	WEP 64/128 bit WPA (TKIP, AES) WPA2 (CCMP, AES) WPA3 WAPI
Wi-Fi operational modes	Station, Access-Point, Wi-Fi direct, or any combination of these
Driver support	Free of charge drivers for Linux and Android RTOS (with certain types of NXP MCUs)
Wi-Fi/Bluetooth coexistence	Internal TDM mechanism

Interfaces

Wi-Fi	SDIO 3.0 (4-bit, up to 150 MHz clock)
Bluetooth	4-wire high-speed UART PCM and I2S for audio
Other	GPIOs

Package

•	
Dimensions	10.4 × 14.3 × 1.8 mm
Mounting	Soldering, 76 pins (LGA)

Environmental data, quality and reliability

Operating temperature -40 °C to +85 °C		
Moisture sensitivity level 4		
RoHS and REACH compliance		

Electrical data

RF power supply	3.0 – 3.6 VDC
I/O power supply	3.3 VDC or 1.8 VDC

Certifications and approvals

	Japan (GITEKI); South Korea (KC) Other certifications will be considered upon request
Bluetooth	v5.2 (Bluetooth BR/EDR and Bluetooth Low
qualification	Energy)

Support products

EVK-MAYA-W161	Evaluation kit for MAYA-W161
EVK-MAYA-W166	Evaluation kit for MAYA-W166

Product variants

MAYA-W160-00B	Professional grade module with two separate U.FL connectors for Wi-Fi and Bluetooth
MAYA-W161-00B	Professional grade module with two separate antenna pins for Wi-Fi and Bluetooth
MAYA-W166-00B	Professional grade module with embedded PCB antenna for Wi-Fi and Bluetooth
MAYA-W166-01B	Professional grade module with single antenna pin for Wi-Fi and Bluetooth

Further information

For contact information, see www.u-blox.com/contact-u-blox.

For more product details and ordering information, see the product data sheet.

Legal Notice:

u-blox or third parties may hold intellectual property rights in the products, names, logos and designs included in this document. Copying, reproduction, or modification of this document or any part thereof is only permitted with the express written permission of u-blox. Disclosure to third parties is permitted for clearly public documents only.

Disclosure to third parties is permitted for clearly public documents only. The information contained herein is provided "as is". No warranty of any kind, either express or implied, is made in relation to the accuracy, reliability, fitness for a particular purpose or content of this document. This document may be revised by u-blox at any time. For most recent documents, please visit www.u-blox.com.