



REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	BATCH PRODUCTION INITIAL RELEASE.	2013.08.22	楊 濤
02	△	依業務要求增加CAP配方	2018.02.08	馮國東




△ The Cap used above 3PIN

Specifications
Current Rating:1.0Amp
Insulation Resistance:1000MΩMin.
Dielectric Withstanding Voltage:300VAC
Contact Resistance:20mΩMax.
Operating Temperature:—40°C to +105°C
Materials
Contact Material:Brass
Insulator Material:High Temperature Thermoplastic, UL 94V—0 LCP or the equivalent material
All materials must meet Greenconn hazardous substances control standards.



Recommended P.C.Board Layout
(Tolerance:±0.05)



Ordering Information

G PEA108 — XX XX A 008 C 1 B X

No. of Pins per Row
02~33

Standard Plating
02=Gold Flash
Selective Plating
01=Tin
05=Gold Flash/Tin

Color
1=Black

Standard Packing
A=Box
Selective Packing
C=Tube
E=CAP+Tube
F=CAP+Tape&Reel

格 菱 股 份 有 限 公 司
Greenconn Corporation

REV.	UNIT.	SCALE.	PAGE.
02	mm	6:1	1/1

GENERAL TOLERANCE	
X.±5.0°	X.±0.30
.X.±3.0°	.X.±0.25
.XX.±2.0°	.XX.±0.15
.XXX.±1.0°	.XXX.±0.10

DESIGNED: 馮國東	DATE: 2018.02.08
CHECKED: 曹 熙	DATE: 2018.02.08
CO SIGNED: 蘭文禮	DATE: 2018.02.08
APPROVED: 李 輝	DATE: 2018.02.08

DWG. NO.	GPEA108—CA8CB
PART NO.	GPEA108—XXXX A008C1BX

TITLE.
1.27 PIN HEADER
SINGLE ROW DIP TYPE
CONNECTOR